








CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	



NOT QUOTED BEVELS	/	MATERIAL	/	TREATMENT	/
-------------------	---	----------	---	-----------	---

MOD. N°	DATE	SIGN.	REPLACES	DATE	SIGN.
SIGNATURE	DATE	SIGN.	REPLACES	DATE	SIGN.

1st DRAW	DESIGN	CHECKED	TOLERANCE	SCALE	UNIT	SHEET	OF
25.08.21	25.08.21		MEDIUM	/	MM	1	3








TITLE	DIMA VK3500 24.0" BOTTOM ARM	RELEASE	A	LEVEL	00
DRAWING N°	DIMA_VK3500_240_BOTTOM				

CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEMI SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	



NOT QUOTED BEVELS				MATERIAL				TREATMENT			
MOD. N°											
DATE											
SIGNATURE											



DATE	1st DRAW	DESIGN	CHECKED
25.08.21	ROMANO	ROMANO	

TOLERANCE	MEDIUM	SCALE	UNIT	SHEET
		/	MM	2 OF 3

TITLE DIMA VK3500 24.0" BOTTOM ARM

DRAWING N° DIMA_VK3500_240_BOTTOM







RELEASE A LEVEL 00

CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	



NOT QUOTED BEVELS		MATERIAL		TREATMENT	
MOD. N°		DATE		REPLACES	DATE
SIGNATURE				REPLACED BY	DATE
1st DRAW		DATE	25.08.21	DESIGN	25.08.21
CHECKED		SIGNATURE	ROMANO		
TOLERANCE		SCALE		UNIT	
MEDIUM		/		MM	
SHEET		OF		3	
TITLE		DIMA VK3500 24.0" BOTTOM ARM		RELEASE	
DRAWING N°		DIMA_VK3500_240_BOTTOM		A	
				LEVEL	
				00	