








"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS /	MATERIAL /	TREATMENT /
------------------------	---------------	----------------

[illegible]

 ASSEFA							
Industria Informatica							
SIGNATURE		1st DRAW	DESIGN	CHECKED	TOLERANCE		
DATE		25.08.21	25.08.21		MEDIUM		
ROMANO		ROMANO					
					SCALE	UNIT	
					/		
						MM	
						SHEET	
						OF	
						1	3

TITLE DIMA VK3500 24.0" TOP ARM








DRAWING N° DIMA_VK3500_240_TOP	RELEASE A	LEVEL 00
--------------------------------	-----------	----------

CONFIDENTIAL—PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS		MATERIAL		TREATMENT	
/		/		/	
MODIFICATION					
MOD. N°				REPLACES	DATE
DATE				REPLACED BY	SIGN. DATE
SIGNATURE					SIGN. DATE

 ASEAN		Industria Informatica	
SIGNATURE		SIGNATURE	
1st DRAW	DESIGN	CHECKED	TOLERANCE
25.08.21	25.08.21		MEDIUM
UNIT		SCALE /	
MM			
SHEET	OF		
2	3		

TITLE DIMA VK3500 24.0" TOP ARM








DRAWING N° DIMA_VK3500_240_TOP	RELEASE	A	LEVEL	00
--------------------------------	---------	---	-------	----

CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

COMMON TOLERANCE	QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS				MATERIAL				TREATMENT			
/				/				/			
MOD. N°				1st DRAW		DESIGN		CHECKED		TOLERANCE	
DATE				25.08.21		25.08.21				MEDIUM	
SIGNATURE				ROMANO		ROMANO				SCALE	
										/	
										UNIT	
										MM	
										SHEET	
										OF	
										3	
										3	