







CONFIDENTIAL-PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

COMMON TOLERANCE	QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		










NOT QUOTED BEVELS				MATERIAL				TREATMENT																			
/				/				/																			
 Industria Informatica				1st DRAW DATE25.08.21 SIGNATUREROMANO				DESIGN 25.08.21 ROMANO				CHECKED				TOLERANCE MEDIUM				SCALE / UNIT MM				 SHEET 1 OF 3			
MODIFICATION				MOD. N°				DATE				SIGNATURE				DATE				SIGNATURE							

CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

COMMON TOLERANCE	QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS				MATERIAL				TREATMENT			
MOD. N°				DATE				REPLACES			DATE
SIGNATURE								REPLACED BY			DATE
											SIGN.

INDUSTRIA INFORMATICA				DATE	1st DRAW	DESIGN	CHECKED	TOLERANCE			
				25.08.21	ROMANO	ROMANO		MEDIUM		SCALE	UNIT
										/	MM
											SHEET
											OF
											3






TITLE DIMA VK3500 24.0" VESA				DRAWING N° DIMA_VK3500_240_VESA				RELEASE	A	LEVEL	00

CONFIDENTIAL—PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		

[illegible]

TITLE	DIMA	VK3500	24.0"	VESA

DRAWING N° DIMA_VK3500_240_VESA

RELEASE

A

LEVEL 00