

CONFIDENTIAL - PROPRIETARY

THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION

NOTE: - ACCURATE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT	
>120	'10'
>30 <120	'20'
>6 <30	'30'
>3 <6	'1.2'
SHORT SIDE	ANGULAR COMMON TOLERANCE

>4000	'5'	'3'
>2000 <4000	'4'	'2'
>1000 <2000	'3'	'1.2'
>315 <1000	'2'	'0.8'
>120 <315	'1.2'	'0.5'
>30 <120	'0.8'	'0.3'
>6 <30	'0.5'	'0.2'
<6	'0.1'	'0.05'
QUALITY	COARSE	MEDIUM
COMMON TOLERANCE	ACCURATE	



