








CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE ±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
	MEDIUM ±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
	ACCURATE ±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS				MATERIAL				TREATMENT			
MOD. N°				DATE				REPLACES			DATE
SIGNATURE								REPLACED BY			DATE
											SIGN.

1st DRAW				DESIGN				CHECKED			
DATE	25.08.21			DATE	25.08.21			DATE			
SIGNATURE	ROMANO			SIGNATURE	ROMANO			SIGNATURE			

TITLE DIMA VK3500 21.5" /BA VESA

DRAWING N° DIMA_VK3500_215BA_VESA

RELEASE A

LEVEL 00

1

2

3

4

5

6

7






8

CONFIDENTIAL—PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS	MATERIAL	TREATMENT
/	/	/

[illegible]

 ASEAN		Industria Informatica	
SIGNATURE		SIGNATURE	
1st DRAWN	DESIGN	CHECKED	TOLERANCE
25.08.21	25.08.21		MEDIUM
ROMANO	ROMANO		
SCALE / 		SHEET OF	
MM		2 3	





TITLE	DIMA VK3500 21.5" /BA VESA	
DRAWING N°	DIMA_VK3500_215BA_VESA	RELEASE A
		LEVEL 00


CONFIDENTIAL—PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS				MATERIAL				TREATMENT					
/				/				/					
MODIFICATION								REPLACES		DATE			
MOD. N°										SIGN.			
DATE										DATE			
SIGNATURE										SIGN.			
 Industria Informatica						1st. DRAW		DESIGN		CHECKED			
						DATE		25.08.21		25.08.21			
						SIGNATURE		ROMANO		ROMANO			
								TOLERANCE		SCALE			
								MEDIUM		/			
										UNIT			
										MM			
										SHEET			
										3			
										OF			
										3			
TITLE DIMA VK3500 21.5" /BA VESA													
DRAWING N° DIMA_VK3500_215BA_VESA						RELEASE		A		LEVEL			
										00			