








CONFIDENTIAL-PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±5
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	±3



NOT QUOTED BEVELS	/	MATERIAL	/	TREATMENT	/
-------------------	---	----------	---	-----------	---

MOD. N°		DATE		REPLACES		DATE	
SIGNATURE				REPLACED BY		DATE	
						SIGN.	

1st DRAW		DESIGN		CHECKED		TOLERANCE		SCALE	
DATE	25.08.21	ROMANO				MEDIUM		/	
SIGNATURE								UNIT	
								MM	
								SHEET	
								1	
								OF	
								3	








TITLE	DIMA VK3500 24.0" /BA BOTTOM ARM	RELEASE	A	LEVEL	00
DRAWING N°	DIMA_VK3500_240BA_BOTTOM				

CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	








CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

COMMON TOLERANCE	QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		



NOT QUOTED BEVELS		MATERIAL		TREATMENT	
MOD. N°		DATE		REPLACES	DATE
SIGNATURE				REPLACED BY	DATE
1st DRAW		DESIGN	CHECKED	TOLERANCE	
25.08.21		ROMANO		MEDIUM	
25.08.21		ROMANO		SCALE	
				UNIT	
				MM	
				SHEET	
				3	
				OF	
				3	

TITLE DIMA VK3500 24.0" / BA BOTTOM ARM		RELEASE		A		LEVEL		00	
DRAWING N° DIMA_VK3500_240BA_BOTTOM									