




12 11 10 9 8 7 6 5 4 3 2 1

H

G

F

E

D

C

B

A

CONFIDENTIAL - PROPRIETARY

THIS DRAWING IS THE PROPERTY OF ASEMA. IT IS NOT TO BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE DESIGN OF ANY OTHER PRODUCT WITHOUT THE WRITTEN PERMISSION OF ASEMA.

NOTE:

- ACCURATE TRIM REQUESTED
- BENDING RADIUS MINIMUM POSSIBLE
- TOLERANCES INDICATED IN ALL DIRECTIONS
- THE DIMENSIONS INCLUDING THE TREATMENT

COMMON TOLERANCE

QUALITY	COARSE	MEDIUM	ACCURATE
>120	>30	>1000	>2000
<120	<30	<1000	<2000
>120	>30	>1000	>2000
<120	<30	<1000	<2000

SHORT SIDE

>3	>6	>30	>120
>3	>6	>30	>120
<3	<6	<30	<120
>3	>6	>30	>120
<3	<6	<30	<120

ANGULAR COMMON TOLERANCE

>1	>30	>10	>10
>1	>30	>10	>10
<1	<30	<10	<10
>1	>30	>10	>10
<1	<30	<10	<10

MATERIAL				THICKNESS	MODIFICATION N°		DATE	
TREATMENT				mm			SIGNATURE	
	1st DRAW	DESIGN	CHECKED	TOLERANCE		SCALE		
	DATE	10/09/2021		MEDIUM		1:4		
	SIGNATURE	Dereani		NOT QUOTED BEVELS		UNIT		
TITLE				NOT QUOTED RADIUS		mm	8 of 9	
DRAWING N°				RELEASE		LEVEL	SIZE	
D18201927				A		00	A2	