




12 11 10 9 8 7 6 5 4 3 2 1

H

G

F

E

D

C

B

A

1 2 3 4 5 6 7 8

A

B

C

D

E

F

G

H

CONFIDENTIAL - PROPRIETARY

THIS DRAWING IS THE PROPERTY OF ASEMI S.p.A. AND IS NOT TO BE REPRODUCED OR COPIED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF ASEMI S.p.A.

NOTE:

- ACCURATE TRIM REQUESTED
- BENDING RADIUS MINIMUM POSSIBLE
- TOLERANCES APPLY TO ALL DIMENSIONS UNLESS OTHERWISE SPECIFIED
- THE DIMENSIONS INCLUDING THE TREATMENT

QUALITY

QUALITY	COARSE	MEDIUM	ACCURATE
>30	>0.5	>0.2	>0.1
<30	<0.5	<0.2	<0.1

SHORT SIDE

SHORT SIDE	>3	>6	>30	>120
COMMON TOLERANCE	<6	<30	<120	<4000

ANGULAR TOLERANCE

ANGULAR TOLERANCE	>3	>6	>30	>120
COMMON TOLERANCE	<6	<30	<120	<4000

QUALITY

QUALITY	COARSE	MEDIUM	ACCURATE
>30	>0.5	>0.2	>0.1
<30	<0.5	<0.2	<0.1

COMMON TOLERANCE

COMMON TOLERANCE	>30	>6	>30	>120
COMMON TOLERANCE	<6	<30	<120	<4000

MATERIAL				THICKNESS mm	MODIFICATION N°		DATE			
TREATMENT							SIGNATURE			
		1st DRAW	DESIGN	CHECKED	TOLERANCE MEDIUM		SCALE 1:4			
		DATE 10/09/2021				NOT QUOTED BEVELS 2x45°		UNIT mm	SHEET 9 of 9	OF
		SIGNATURE Dereani				NOT QUOTED RADIUS R2				
TITLE DIMA VK3500P-BA 24,0" BOTTOM ARM CON MANIGLIE E PORTA TASTIERA										
DRAWING N° D18201927					RELEASE A		LEVEL 00		SIZE A2	