




CONFIDENTIAL - PROPRIETARY
THIS DRAWING IS THE PROPERTY OF ASEMI. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS NOT TO BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE DESIGN OF OTHER PRODUCTS WITHOUT WRITTEN PERMISSION.

NOTE:
- ACCURATE TRIM REQUESTED
- BENDING RADIUS MINIMUM POSSIBLE
- BENDING RADIUS AND PARALLEL GEOMETRIC TOLERANCE MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS INCLUDING THE TREATMENT
- THE DIMENSIONS INCLUDING THE TREATMENT

QUALITY	COMMON	COARSE	MEDIUM	ACCURATE
>6	<6	0.2	0.1	0.05
>30	<30	0.5	0.2	0.1
>120	<120	0.8	0.3	0.15
>300	<300	1.2	0.5	0.2
>315	<315	2	0.8	0.3
>1000	<1000	3	1.2	0.5
>2000	<2000	4	2	0.8
>4000	<4000	5	3	1

SHORT SIDE	ANGULAR COMMON TOLERANCE
>3	1°
>6	1°
>30	1°
>120	1°
>300	1°
>1200	1°
>4000	1°

MATERIAL				THICKNESS	MODIFICATION N°		DATE	
TREATMENT				mm			SIGNATURE	
	1st DRAW	DESIGN	CHECKED	TOLERANCE		SCALE		
	DATE	10/09/2021		MEDIUM		1:4		
	SIGNATURE	Dereani		NOT QUOTED BEVELS		2x45°		
TITLE				UNIT		mm	SHEET	
DIMA VK3500P-BA 24.0" BOTTOM ARM CON MANIGLIE				NOT QUOTED RADIUS		R2	OF	
DRAWING N°				RELEASE		A	LEVEL	
D18201927							00	
							SIZE	
							A2	