

CONFIDENTIAL - PROPRIETARY








THIS DRAWING IS THE PROPERTY OF ASEMA. IT IS TO BE USED FOR THE DESIGN AND CONSTRUCTION OF THE PRODUCT ONLY. IT IS NOT TO BE REPRODUCED OR COPIED OR USED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF ASEMA.

NOTE:
- ACCURATE TRIM REQUESTED
- BENDING RADIUS MINIMUM POSSIBLE
- TOLERANCES SHOWN ARE FOR THE TREATMENT OF ALL DIRECTIONS
- THE DIMENSIONS INCLUDING THE TREATMENT

SHORT SIDE	>3	>6	>30	>120
ANGULAR COMMON TOLERANCE	<6	<30	<120	>120
	1°	30'	20'	10'

QUALITY	>30	>120	>315	>1000	>2000	>4000
COMMON	<6	<30	<315	<1000	<2000	<4000
TOLERANCE	0.2	0.5	0.8	1.2	2	3
	0.1	0.2	0.3	0.5	0.8	1.2
	0.05	0.1	0.15	0.2	0.3	0.5

DETTAGLIO A
SCALA 1 : 2



MATERIAL				THICKNESS	MODIFICATION N°		DATE
TREATMENT				mm			SIGNATURE
	1st DRAW	DESIGN	CHECKED	TOLERANCE	MEDIUM	SCALE	1:4
	DATE	10/09/2021		NOT QUOTED BEVELS	2x45°	UNIT	mm
	SIGNATURE	Dereani		NOT QUOTED RADIUS	R2	SHEET	2 of 9
TITLE DIMA VK3500P-BA 24,0" VESA CON MANIGLIA INFERIORE							
DRAWING N° D18201927				RELEASE	A	LEVEL	00
						SIZE	A2