





5	6	7	8
SPECIFICATIONS			
CERTIFICATIONS	UL RECOGNIZED AND CSA CERTIFIED		
COUPLING NUT MATERIAL	EPOXY-COATED ZINC		
CONNECTOR OVERMOLD MATERIAL	OIL RESISTANT PUR		
CONTACT PLATING	GOLD OR GOLD FLASH OVER PALLADIUM-NICKEL		
CONTACT MATERIAL	BRASS OR COPPER ALLOY		
CABLE TYPE	PVC, 22AWG, 300V		
CABLE JACKET COLOR	YELLOW		
BEND RADIUS	10 X DIAMETER		
NUMBER OF CONDUCTORS [AWG]	4x22 AWG		
SHIELDING	BRAIDED		
CABLE RATING	UL AWM STYLE 2661 VW-1 105C 300V, CSA AWM A/B 1/II 80C 300V FT1, UV OIL AND WATER RESISTANT		
INGRESS PROTECTION	IP67, NEMA 6P		
TEMPERATURE RATING	-20° ... +105°C (-4° ... +221°F)		



NOTES:
1. (*) REPRESENTS THE CABLE LENGTH IN METERS.
2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.

DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>