

1

2

3

4

5

6

7


8

MALE END VIEW

4-BLACK

1-BROWN

3-BLUE




3-PIN, M8 X 1
STRAIGHT MALE CONNECTOR

FEMALE END VIEW

4-BLACK

3-BLUE

1-BROWN



3-PIN, M8 X 1
STRAIGHT FEMALE CONNECTOR

CERTIFICATIONS

UL RECOGNIZED AND CSA CERTIFIED

COUPLING NUT MATERIAL

NICKEL PLATED BRASS

CONNECTOR OVERMOLD MATERIAL

OIL RESISTANT PUR

CONTACT PLATING

GOLD OVER NICKEL-PLATED BRASS

CONTACT MATERIAL

BRASS OR COPPER ALLOY

CABLE TYPE

TPE, 24AWG, 300V

CABLE JACKET COLOR

YELLOW

BEND RADIUS

10 X DIAMETER

NUMBER OF CONDUCTORS [AWG]

3X24 AWG (PICO MALE), 3X24 AWG (PICO FEMALE)

SHIELDING

UNSHIELDED

CABLE RATING

UL AWM STYLE 20327 VW-1 105°C 300V FT1

INGRESS PROTECTION

IP67

TEMPERATURE RATING

-20°... +105°C (-4°... +221°F)

M8 X 1

Ø 8.6
[.34]

41,5
[1.63]

Ø 4,3
[.17]

35
[1.37]

Ø 10.6
[.42]