

	1	2	3	4	5	6	7	8
A	MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS			
					CERTIFICATIONS		UL RECOGNIZED AND CSA CERTIFIED	
					COUPLING NUT MATERIAL		NICKEL PLATED BRASS	
B					CONNECTOR OVERMOLD MATERIAL		OIL RESISTANT PUR	
					CONTACT PLATING		GOLD OVER NICKEL-PLATED BRASS	
					CONTACT MATERIAL		BRASS OR COPPER ALLOY	
C					CABLE TYPE		PUR, 24AWG, 300V	
					CABLE JACKET COLOR		YELLOW	
					BEND RADIUS		10 X DIAMETER	
D					NUMBER OF CONDUCTORS [AWG]		3X24 AWG (PICO MALE), 3X24 AWG (PICO FEMALE)	
					SHIELDING		UNSHIELDED	
					CABLE RATING		UL AWM STYLE 20233, 21198 OR 10493 80°C 300V FT2	
E					INGRESS PROTECTION		IP67	
					TEMPERATURE RATING		-20°... +80°C (-4°... +176°F)	
F								
G								
H								

NOTES:

1. (*) REPRESENTS THE CABLE LENGTH IN METERS.

2. ALL DIMENSIONS ARE IN MM [INCHES] UNLESS AND OTHERWISE SPECIFIED.

DIMENSIONS & INFORMATION SHOWN ARE FOR REFERENCE ONLY AND FOR LATEST UPDATE PLEASE REFER <http://www.ab.com/catalogs/>

Rockwell Automation		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC., AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
889P-B3UBPM-*		Sheet 1 Of 1	
Drawn by: LNT	Date: 04-10-2015	C	889P-B3UBPM-* 0.0