

# Spring-Clamp Connection Terminal Blocks

## Mini-Blocks, Panel-Mount

	1492-LMP3 ❄			1492-LMP3Q ❄		
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> One end block and one end barrier or two end barriers must be used on each end of a terminal bank to provide mounting slots.						
<b>Specifications</b>	<i>Mini surface mount feed-through Terminal Block</i>			<i>Mini 4 point, surface mount, Feed-through Terminal Block</i>		
Certifications		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>
Voltage Rating	600V AC/DC		800V AC/DC	600V AC/DC		800V AC/DC
Maximum Current	20 A	25 A	24 A	20 A	25 A	24 A
Wire Range (Rated Cross Section)	#26...12 AWG		2.5 mm <sup>2</sup>	#26...12 AWG		2.5 mm <sup>2</sup>
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)		
Density	59 pcs/ft (196 pcs/m)			30 pcs/ft (99 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Color	Grey	<b>1492-LMP3</b>	100	<b>1492-LMP3Q</b>	100	
	Blue	1492-LMP3-B	100	<b>1492-LMP3Q-B</b>	100	
End Terminal Blocks (with Mounting Brackets)						
Color	Grey	<b>1492-LMP3E</b>	50	1492-LMP3QE	50	
	Blue	1492-LMP3E-B	50	1492-LMP3QE-B	50	
<b>Accessories</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Mounting Foot*	1492-MFLM	50		1492-MFLM	50	
Jumpers						
Side Center Jumper — 2-Pole	<b>1492-SJLM5-2</b>	50		<b>1492-SJLM5-2</b>	50	
Side Jumper Installation Tool	<b>1492-TAL5-2</b>	1		<b>1492-TAL5-2</b>	1	
End Barriers (with Mounting Slots)						
	Grey	<b>1492-EBLMP3</b>	50	<b>1492-EBLMP3</b>	50	
	Blue	1492-EBLMP3-B	50	1492-EBLMP3-B	50	
Marking Systems						
Snap-In Marker Cards	<b>1492-M5X10</b> (144/card)	5		<b>1492-M5X10</b> (144/card)	5	
Snap-In Marker Cards	<b>1492-M5X5</b> (200/card)	5		<b>1492-M5X5</b> (200/card)	5	
Hinged Marker Cards	<b>1492-MH5X10</b> (96/card)	5		<b>1492-MH5X10</b> (96/card)	5	

❄ For a grouping of terminal blocks, use 1 end terminal block, select the number of terminal blocks, and use 1 end barrier. You can also use a group of terminal blocks with an end barrier on each end.

\* Allows mounting to 15 mm and 35 mm DIN Rail. Recommended spacing is every fifth block on Cat. No. 1492-LMP3 and every third block on Cat. No. 1492-LMP3Q.