

LEVEL	I/O CAT. NO.	MODULE LABEL																			
UPPER	1769-HSC USE WITH 1492-AIFMCE4-F	OUT +DC	OUT +DC	+A0	-A0	+B0	-B0	+Z0	-Z0	+A1	-A1	+B1	-B1	+Z1	-Z1	OUT 0	OUT 1	OUT 2	OUT 3	OUT COM	OUT COM
LOWER		+V E0	+V E0F	COM E0	COM E0	+V E1	+V E1F	COM E1	COM E1	BUS A		BUS B		SHIELD							
UPPER	1756-HSC (12-24V or 5V) USE WITH 1492-AIFMCE4-F	+DC 0	+DC 1	A0	A0	B0	B0	Z0	Z0	A1	A1	B1	B1	Z1	Z1	OUT 0	OUT 1	OUT 2	OUT 3	COM 0	COM 1
LOWER		+V E0	+V E0F	COM E0	COM E0	+V E1	+V E1F	COM E1	COM E1	BUS A		BUS B		SHIELD							
UPPER	1746-HSCE USE WITH 1492-AIFMCE4-F	+V DC	+V DC	+A	-A	+B	-B	+Z	-Z	LS 24V	LS COM	LS 12V	LS COM	LS 5V	OUT 0	OUT 1	OUT 2	OUT 3	COM COM	COM COM	
LOWER		+V E0	+V E0F	COM E0	COM E0	+V E1	+V E1F	COM E1	COM E1	BUS A		BUS B		SHIELD							
UPPER	1746-HSCE2 USE WITH 1492-AIFMCE4-F	+V DC	+V DC	+A	-A	+B	-B	+Z	-Z	+A	-A	+B	-B	+Z	-Z	OUT 0	OUT 1	OUT 2	OUT 3	COM COM	COM COM
LOWER		+V E0	+V E0F	COM E0	COM E0	+V E1	+V E1F	COM E1	COM E1	BUS A		BUS B		SHIELD							
UPPER	1769-HSC USE WITH 1492-AIFMCE4	OUT +DC	OUT +DC	+A0	-A0	+B0	-B0	+Z0	-Z0	+A1	-A1	+B1	-B1	+Z1	-Z1	OUT 0	OUT 1	OUT 2	OUT 3	OUT COM	OUT COM
LOWER		+V E0	+V E0	COM E0	COM E0	+V E1	+V E1	COM E1	COM E1	BUS A		BUS B		SHIELD							
UPPER	1756-HSC (12-24V or 5V) USE WITH 1492-AIFMCE4	+DC 0	+DC 1	A0	A0	B0	B0	Z0	Z0	A1	A1	B1	B1	Z1	Z1	OUT 0	OUT 1	OUT 2	OUT 3	COM 0	COM 1
LOWER		+V E0	+V E0	COM E0	COM E0	+V E1	+V E1	COM E1	COM E1	BUS A		BUS B		SHIELD							
UPPER	1746-HSCE USE WITH 1492-AIFMCE4	+V DC	+V DC	+A	-A	+B	-B	+Z	-Z	LS 24V	LS COM	LS 12V	LS COM	LS 5V	OUT 0	OUT 1	OUT 2	OUT 3	COM COM	COM COM	
LOWER		+V E0	+V E0	COM E0	COM E0	+V E1	+V E1	COM E1	COM E1	BUS A		BUS B		SHIELD							
UPPER	1746-HSCE2 USE WITH 1492-AIFMCE4	+V DC	+V DC	+A	-A	+B	-B	+Z	-Z	+A	-A	+B	-B	+Z	-Z	OUT 0	OUT 1	OUT 2	OUT 3	COM COM	COM COM
LOWER		+V E0	+V E0	COM E0	COM E0	+V E1	+V E1	COM E1	COM E1	BUS A		BUS B		SHIELD							
UPPER	PowerFlex 700S/W 1492-AIFMCE4-F			+A	-A	+B	-B	+Z	-Z	+ - +10V COM -10V COM											
LOWER		+V E0	+V E0F							BUS A		BUS B		SHIELD							
UPPER	PowerFlex 700S/W 1492-AIFMCE4			+A	-A	+B	-B	+Z	-Z	+ - +10V COM -10V COM											
LOWER										BUS A		BUS B		SHIELD							