


152C-D31JBD-J60-4RG-6P



NOTES:

- 1
- USE 75°C CU WIRE ONLY
- 2
- LINE FUSES SUPPLIED BY CUSTOMER WHEN DISCONNECT SWITCH IS SUPPLIED. REFER TO NEC WHEN SELECTING SHORT CIRCUIT PROTECTION
- 3
- ADDITIONAL CONTROL CIRCUIT OVERCURRENT PROTECTION REQUIRED FOR NON-COMBINATION STARTERS. REFER TO NATIONAL ELECTRIC CODE.
- 4
- DIP SWITCH DEFAULT FACTORY SETTINGS
- 1= O 9= O
- 2= I 10= O
- 3= O 11= I
- 4= O 12= O
- 5= I 13= O
- 6= O 14= O
- 7= O 15= I
- 8= O 16= O

Wire Connector Torque	
Line Terminal (Lb.In.)	Load Terminal (Lb.In.)
500	375

AB

QUALITY

Rockwell

Automation

Title:

SMC COMBO

CATALOG NO.

152C-D31JBD-J60-4RG-6P

Drawn by:

AUTO_GEN

Date:

12/23/17

Sheet:

1 of 2

Ver:

00

Size:

D

CONFIDENTIAL AND PROPRIETARY INFORMATION: THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC., AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

S.O.