


153C-D20JCD-D25-1-6P



NOTES:

- 1
- USE 75°C CU WIRE ONLY
- 2
- LINE FUSES SUPPLIED BY CUSTOMER WHEN
DISCONNECT SWITCH IS SUPPLIED. REFER TO
NEC WHEN SELECTING SHORT CIRCUIT
PROTECTION
- 3
- ADDITIONAL CONTROL CIRCUIT OVERCURRENT
PROTECTION REQUIRED FOR NON-COMBINATION
STARTERS. REFER TO NATIONAL ELECTRIC CODE.
- 4
- DIP SWITCH DEFAULT FACTORY SETTINGS
1= O 9= O
2= I 10= O
3= O 11= I
4= O 12= O
5= I 13= O
6= O 14= O
7= O 15= I
8= O 16= O

Wire Connector Torque	
Line Terminal (Lb.In.)	Load Terminal (Lb.In.)
88	275

 Rockwell Automation		CONFIDENTIAL AND PROPRIETARY INFORMATION: THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC., AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.		
Title: SMC COMBO		S.O.		
CATALOG NO.				
153C-D20JCD-D25-1-6P				
Drawn by: AUTO_GEN	Date: 12/29/17	Sheet: 1 of 2	Ver: 00	Size: D