


153C-D25JCD-D40-1-4RG-6P



NOTES:

- 1
- USE 75°C CU WIRE ONLY
- 2
- LINE FUSES SUPPLIED BY CUSTOMER WHEN
DISCONNECT SWITCH IS SUPPLIED. REFER TO
NEC WHEN SELECTING SHORT CIRCUIT
PROTECTION
- 3
- ADDITIONAL CONTROL CIRCUIT OVERCURRENT
PROTECTION REQUIRED FOR NON-COMBINATION
STARTERS. REFER TO NATIONAL ELECTRIC CODE.
- 4
- DIP SWITCH DEFAULT FACTORY SETTINGS
1= O 9= O
2= I 10= O
3= O 11= I
4= O 12= O
5= I 13= O
6= O 14= O
7= O 15= I
8= O 16= O

Wire Connector Torque	
Line Terminal (Lb.In.)	Load Terminal (Lb.In.)
220	275

AB

QUALITY

Rockwell

Automation

Title:

SMC COMBO

CATALOG NO.

153C-D25JCD-D40-1-4RG-6P

Drawn by:

AUTO_GEN

Date:

01/03/18

Sheet:

1 of 2

Ver:

00

Size:

D

CONFIDENTIAL AND PROPRIETARY INFORMATION:
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION,
INC., AND MAY NOT BE USED, COPIED OR DISCLOSED TO
OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN
PERMISSION OF ROCKWELL AUTOMATION, INC.

S.O.