153F-D13JCD-D25-20E-HC3

550V/600V
3PH 50Hz/60Hz
L1 L2 L3

CB1
L1 1L1
L2 1L2
L3 1L3

L1 BLK L2 BLK
TB1 L1 TB1 L2

HMI
SCANBUS PORT

SMC-FLEX
PORT 2
L1/1 T1/2
L2/3 T2/4
L3/5 T3/6
SMC
SMC POWER TERMINALS (SEE MANUAL)

+REMOTE
MTR1
U1
V1
W1
M
3 ~
PE
GRD

SEPARATE CONTROL
4

SMC 11 QC L
QC LT
QC N
QC N
SMC 12
SMC 13

QC L
QC 4
SR A1 A2
QC 3
SR 11 14
QC 5
+REMOTE
QC 4
*
SMC 18
SR 21 24
QC L
QC 8
SMC 16
SMC 17
SMC 14
14 GRN MTG_PLT
GRD
SMC (AUX 1) 19 20
QC P1
SMC (AUX 2) 29 30
QC F
SMC (AUX 4) 33 34
P2 QC
QC N

FAN
L RED 1 2 3 4 13 WHT

NOTES:

* ADD JUMPER FROM TERMINAL BLOCK "18" TO TERMINAL BLOCK "5" WHEN USING DPI (-HC3 or -20*) JUMPER IS INCLUDED IN RAIL IN TERMINAL BLOCK 18.

** REMOVE PRE-INSTALLED YELLOW JUMPER BETWEEN TERMINAL BLOCK "L" AND TERMINAL BLOCK"8" WHEN USING AUX COMMAND DEVICE

1 SMC FACTORY PRE-PROGRAMMED PARAMETERS;
PARAMETER 109: AUX4CFG SET TO NORMAL NC
TO NORMAL NC

2 USE 75ºC CU WIRE ONLY

3 LINE FUSES SUPPLIED BY CUSTOMER WHEN DISCONNECT SWITCH IS SUPPLIED. REFER TO NEC WHEN SELECTING SHORT CIRCUIT PROTECTION

4 ADDITIONAL CONTROL CIRCUIT OVERCURRENT PROTECTION REQUIRED FOR NON-COMBINATION STARTERS. REFER TO NATIONAL ELECTRIC CODE.

5 FOR UNITS WITH DPI (HIM OR COMM CARD), SET LOGIC MASK (PARAMETER 87) TO "0010 0100"

***

Wire Connector Torque	
Line Terminal (Lb.In.)	Load Terminal (Lb.In.)
88	275

Rockwell Automation

CONFIDENTIAL AND PROPRIETARY INFORMATION: THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC., AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

Title: SMC COMBO

S.O.

CATALOG NO. 153F-D13JCD-D25-20E-HC3

Drawn by: AUTO_GEN | **Date:** 02/16/18 | **Sheet:** 1 of 2 | **Ver:** 00 | **Size:** D