




NOTES:
1. ENCLOSURE SYSTEM IS 2000MM AND 600MM DEEP
2. PLEASE CHECK ROCKWELLAUTOMATION.LITERATURE.COM FOR ADDITIONAL INFORMATION ON THE POWERFLEX 755T DRIVES.

2. DRIVE SIZE SHOWN:	INPUT VOLTAGE	NORMAL DUTY RATING
	400	2447 kW
	480	2705 kW
	600	2488 kW
	690	2647 kW

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCING IN ACCORDANCE WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC AND CONTROLLED BY THE CAD MODELS AND CONTROLLED SIMULTANEOUSLY

Rockwell Automation

PF755,FR14,TM,BS,INLINE,INSTL
INLINE INSTALLATION SPECIFICATION

DRAWN BY: MLACHAW

DATE: 10-26-2017


CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.

Sheet 1 Of 2

SIZE: D

DIR: 10003487332

VER: 00



NOTES:
1. GROUND BUSBARS ARE 10MM THICK

DIMENSIONS IN MM
UNLESS OTHERWISE SPECIFIED
DIMENSIONS & TOLERANCES IN ACCORDANCE
WITH ASME Y14.5-2009
ALL UNTOLERANCED DIMENSIONS ARE BASIC
AND CONTROLLED BY THE CAD MODELS AND
CONTROLLED SIMULTANEOUSLY

Rockwell Automation		CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
PF755,FR14,TM,BS,INLINE,INSTL INLINE INSTALLATION SPECIFICATION		Sheet 2 Of 2	
SIZE	DIR	10003487332	VER
D			00
DRAWN BY: MLACHAW		DATE: 10-26-2017	