




APPROX. WEIGHT (LBS)  
3

ECO No	DESCRIPTION	REV BY	DATE


CRITICAL TO QUALITY CLASSIFICATION TABLE				
P-PROPOUNCE FIT ASSEMBLY E-ENGINEERING APPLICABLE CLASSIFICATIONS S-SCHEMATIC AND/OR MANUFACTURING REQUIREMENT R-REGULATORY REQUIREMENT/COMPLIANCE IS MANDATORY				
COMMENTS	DRAWING ZONE	Ⓟ	Ⓡ	Ⓢ
ROHS	G1-H1			X




TOP VIEW




BOTTOM VIEW



FRONT VIEW



SIDE VIEW



CUSTOMER CONNECTION DETAIL VIEW

- NOTES:**
1. TERMINAL WIRE RANGE: 10-22 AWG.
  2. TERMINAL SCREW TIGHTENING TORQUE: 4 IN.LBS.
  3. REFER TO USER MANUAL FOR COMPLETE INSTALLATION INSTRUCTIONS.

THE COMPONENT, PART OR ASSEMBLY DESCRIBED IN THIS DOCUMENT MUST COMPLY WITH THE EU (EUROPEAN UNION) DIRECTIVE RoHS2		MATERIAL		CONFIDENTIAL AND PROPRIETARY INFORMATION THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF MTE CORPORATION AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF MTE CORPORATION													
CONTAINS <0.1% OF ANY SVHC BY WEIGHT PER REACH REGULATION				DESCRIPTION LINE/LOAD REACTOR (2AMPS 20 mH)													
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES [MM] TOLERANCES ARE: ANGLES: ± 1° 1 PLACE .X: ± .1 [2.5] 2 PLACE .XX: ± .03 [0.76] 3 PLACE .XXX: ± .010 [0.254]				<table border="1"> <tr> <td>DRAWN</td> <td>DATE</td> </tr> <tr> <td>WF</td> <td>01/22/20</td> </tr> <tr> <td>CHECKED</td> <td>DATE</td> </tr> <tr> <td>WF</td> <td>01/23/20</td> </tr> <tr> <td>APPROVED</td> <td>DATE</td> </tr> <tr> <td>PY</td> <td>01/24/20</td> </tr> </table>		DRAWN	DATE	WF	01/22/20	CHECKED	DATE	WF	01/23/20	APPROVED	DATE	PY	01/24/20
DRAWN	DATE																
WF	01/22/20																
CHECKED	DATE																
WF	01/23/20																
APPROVED	DATE																
PY	01/24/20																
SCALE 3:2		DWG No. CD 1321-3R2-B		REV 00													
				SHEET 1 OF 1													