




APPROX. WEIGHT (LBS)
26



FRONT VIEW
(PANEL REMOVED)




SIDE VIEW




ECO No	DESCRIPTION	REV BY	DATE

CRITICAL TO QUALITY CLASSIFICATION TABLE				
<small> P-PERFORMANCE FIT ASSEMBLY F-FITTED/APPLICABLE CLASSIFICATIONS S-ENGINEERING MANUFACTURING REQUIREMENT R-REGULATORY REQUIREMENT/COMPLIANCE MANDATORY </small>				
COMMENTS	DRAWING ZONE	P	F	R
ROHS	G1-H1			X




BOTTOM VIEW




TOP VIEW
(PANEL REMOVED)

#10-32 GROUND STUD



SEE NOTE 1



DETAIL A
CUSTOMER CONNECTION
DETAIL VIEW

SEE NOTE 2

NOTES:

1. TERMINAL WIRE RANGE: 4-14 AWG.
2. TERMINAL SCREW TIGHTENING TORQUE: 16 IN/LBS.
3. REFER TO USER MANUAL FOR COMPLETE INSTALLATION INSTRUCTIONS.

THE COMPONENT, PART OR ASSEMBLY DESCRIBED IN THIS DOCUMENT MUST COMPLY WITH THE EU (EUROPEAN UNION) DIRECTIVE RoHS2 <small>CONTAINS <0.1% OF ANY SVHC BY WEIGHT PER REACH REGULATION</small>		MATERIAL		CONFIDENTIAL AND PROPRIETARY INFORMATION <small>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF MTE CORPORATION AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF MTE CORPORATION</small>		
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES [MM] TOLERANCES ARE:</small> ANGLES: ± 1° 1 PLACE .X: ± .1 [2.5] 2 PLACE .XX: ± .03 [0.76] 3 PLACE .XXX: ± .010 [0.254]				DESCRIPTION LINE/LOAD REACTOR w/ENCL SURE		
DRAWN WF	DATE 01/22/20			SIZE D	DWG No. CD 1321-3RA35-A	REV 00
CHECKED WF	DATE 01/23/20			SCALE 1:2	SHEET 1 OF 1	
APPROVED PY	DATE 01/24/20					