







Spring-Clamp Connection Terminal Blocks

Plug-in Style Blocks (Cat. Nos. 1492-L3P, -LDG3P) and Analog Loop Control Block (Cat. No. 1492-LDAG3)

	1492-L3P			1492-LDG3P			1492-LDAG3		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.									
Specifications	Single Circuit Plug-In Component Block for a Variety of Components			Terminal Block with slot for Plug-In Component, Feed-Through Circuit and 1 Ground Connection			Analog Loop Control Terminal Block with 2 Feed-Through Circuits and 1 Ground Connection		
Certifications		CSA	IEC		CSA	IEC		CSA	IEC
Voltage Rating	600V AC/DC		500V AC/DC	300V AC/DC		250V AC/DC	300V AC/DC		250V AC/DC
Maximum Current	20 A		24 A	10 A		20 A	10 A		24 A
Wire Range (Rated Cross Section)	#30...12 AWG		4 mm ²	#26...12 AWG		2.5 mm ²	#26...12 AWG		2.5 mm ²
Wire Strip Length	0.39 in. (10 mm)			0.31 in. (8 mm)			0.31 in. (8 mm)		
Density	59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.			
Color	Grey								
	1492-L3P	25	1492-LDG3P	25	1492-LDAG3	25			
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.			
Mounting Rails									
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10			
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10			
1 m Hi-Rise Symmetrical DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2			
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2			
End Barrier	1492-EBL3	50	1492-EBLDAG3	20	1492-EBLDAG3	20			
End Anchors and Retainers									
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20			
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100			
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50			
Jumpers									
Plug-In Center Jumper — 50-pole	1492-CJK5-50	10	1492-CJLJ5-50	10	1492-CJLJ5-50	10			
Plug-In Center Jumper — 10-pole	1492-CJK5-10	20	1492-CJLJ5-10	20	1492-CJLJ5-10	20			
Plug-In Center Jumper — 9-pole	1492-CJK5-9	20	1492-CJLJ5-9	20	1492-CJLJ5-9	20			
Plug-In Center Jumper — 8-pole	1492-CJK5-8	20	1492-CJLJ5-8	20	1492-CJLJ5-8	20			
Plug-In Center Jumper — 7-pole	1492-CJK5-7	20	1492-CJLJ5-7	20	1492-CJLJ5-7	20			
Plug-In Center Jumper — 6-pole	1492-CJK5-6	20	1492-CJLJ5-6	20	1492-CJLJ5-6	20			
Plug-In Center Jumper — 5-pole	1492-CJK5-5	20	1492-CJLJ5-5	20	1492-CJLJ5-5	20			
Plug-In Center Jumper — 4-pole	1492-CJK5-4	60	1492-CJLJ5-4	60	1492-CJLJ5-4	60			
Plug-In Center Jumper — 3-pole	1492-CJK5-3	60	1492-CJLJ5-3	60	1492-CJLJ5-3	60			
Plug-In Center Jumper — 2-pole	1492-CJK5-2	60	1492-CJLJ5-2	60	1492-CJLJ5-2	60			
Other Accessories									
Disconnect Plug	1492-DPL	50	1492-DPL	50	—	—			
Component Plug	1492-CPL	50	1492-CPL	50	—	—			
Fuse Plug	1492-FPK2	20	1492-FPK2	20	—	—			
Without Blown Fuse Indicator									
10...36V Blown Fuse Indicator	1492-FPK224	20	1492-FPK224	20	—	—			
35...70V Blown Fuse Indicator	1492-FPK248	20	1492-FPK248	20	—	—			
60...150V Blown Fuse Indicator	1492-FPK2120	20	1492-FPK2120	20	—	—			
140...250V Blown Fuse Indicator	1492-FPK2250	20	1492-FPK2250	20	—	—			
Reducing Sleeves 28...24 AWG (0.13...0.2 mm ²) White	1492-PSL3-2	100	—	—	—	—			
Reducing Sleeves 22...20 AWG (0.25...0.5 mm ²) Grey	1492-PSL3-5	100	—	—	—	—			
Reducing Sleeves 18 AWG (0.75...1.0 mm ²) Dark Grey	1492-PSL3-10	100	—	—	—	—			
Test Plug	1492-TPL5	25	1492-TP23	20	—	—			
Electrical Warning Plate	1492-EWPL5	20	—	—	—	—			
Group Marking Carrier	1492-GM35	25	1492-GM35	25	1492-GM35	25			
Marking Systems									
Snap-In Marker Cards	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5			
Snap-In Marker Cards	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5			