

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L6				1492-L6T				1492-L10			
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.												
Specifications	Feed-through terminal block				Feed-through terminal block with 2 connection points on one side				Feed-through terminal block			
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC	ATEX
Voltage Rating	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC
Maximum Current	50 A		41 A	36 A	50 A		41 A	36 A	60 A	55 A	57 A	50 A
Wire Range (Rated Cross Section)	#22...8 AWG	#20...8 AWG	6 mm ²	6 mm ² (20...8 AWG)	#22...8 AWG	#20...8 AWG	6 mm ²	6 mm ² (#20...10 AWG)	#16...6 AWG		10 mm ²	10 mm ² (16...8 AWG)
Wire Strip Length	0.51 in. (13 mm)				0.51 in. (13 mm)				0.70 in. (18 mm)			
Density	37 pcs/ft (123 pcs/m)				37 pcs/ft(123 pcs/m)				30 pcs/ft (99 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Short-Circuit Current Rating	See page 12-78											
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color	Grey	1492-L6	50	1492-L6T	50	1492-L10	25					
	Red	1492-L6-RE	50	1492-L6T-RE	50	1492-L10-RE	25					
	Blue	1492-L6-B	50	1492-L6T-B	50	1492-L10-B	25					
	Black	1492-L6-BL	50	1492-L6T-BL	50	1492-L10-BL	25					
	Green	1492-L6-G	50	1492-L6T-G	50	1492-L10-G	25					
	Yellow	1492-L6-Y	50	1492-L6T-Y	50	1492-L10-Y	25					
	Orange	1492-L6-OR	50	1492-L6T-OR	50	1492-L10-OR	25					
	Brown	1492-L6-BR	50	1492-L6T-BR	50	1492-L10-BR	25					
	White	1492-L6-W	50	1492-L6T-W	50	1492-L10-W	25					
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails												
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10						
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10						
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2						
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2						
End Barriers	Grey	1492-EBL6	50	1492-EBL6T	50	1492-EBL10	20					
	Blue	1492-EBL6-B	50	1492-EBL6T-B	50	1492-EBL10-B	20					
	Yellow	1492-EBL6-Y	50	1492-EBL6T-Y	50	1492-EBL10-Y	20					
End Anchors and Retainers												
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20						
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100						
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50						
Jumpers												
Plug-in Center Jumper — 32-Pole	1492-CJL8-32	10	1492-CJL8-32	10								
Plug-in Center Jumper — 4-Pole	1492-CJL8-4	60	1492-CJL8-4	60								
Plug-in Center Jumper — 3-Pole	1492-CJL8-3	60	1492-CJL8-3	60								
Plug-in Center Jumper — 2-Pole	1492-CJL8-2	60	1492-CJL8-2	60	1492-CJL10-2	25						
Other Accessories												
Test Plug							1492-TP23	20				
Test Plug (Stackable)	1492-TPL8	25	1492-TPL8	25								
Electrical Warning Plate	1492-EWPL8	20	1492-EWPL8	20			1492-EWPL10	20				
Marking Systems												
Snap-In Marker Cards*	1492-M6X12 (120/card)	5	1492-M6X12 (120/card)	5	1492-M6X12 (120/card)	5						
Snap-In Marker Cards	1492-MR8X12 (84/card)	5	1492-M8X5 (160/card)	5	1492-M8X5 (160/card)	5						
Hinged Marker Cards	1492-MH6X12 (80/card)	5	1492-MH6X12 (80/card)	5	1492-MH5X15 (96/card)	5						

* May only be mounted in terminal block corner marking positions.