









	1492-H...	1492-WFB4...		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.				
Specifications	Single-circuit fusible terminal block with or without fuse indication.	Single-circuit fuse block with or without fuse indication.		
Certifications	  	  		
Voltage Rating	H6/WFB4: 300V AC/DC H5/WFB424: 10...57V AC/DC H4/WFB4250: 100...300V AC	H6/WFB4: 300V AC/DC H5/WFB424: 10...57V AC/DC H4/WFB4250: 85...264V AC		
Maximum Current	15 A	15 A		
Wire Range (Rated Cross Section)	#30...12 AWG 0.5...4 mm ²	#30...12 AWG 0.5...4 mm ²		
Wire Strip Length	0.38 in. (9.7 mm)	0.31 in. (8 mm)		
Recommended Tightening Torque	7.1 lb•in. (0.8 N•m)	2.65...5.3 lb•in. (0.3...0.6 N•m)		
Density	33 pcs/ft (109pcs/m)	38 pcs/ft (125 pcs/m)		
Housing Temperature Range	-40...+195 °F (-40...+90 °C)	-40...+195 °F (-40...+90 °C)		
Indicator Type				
H6/WFB4	Non-Indicating	Non-Indicating		
H5/WFB424	Red LED	Red LED		
H4/WFB4250	Neon	Neon		
Leakage Current				
H6/WFB4	—	—		
H5/WFB424	2 mA @ 24V	2 mA @ 24V		
H4/WFB4250	2 mA @ 300V	2 mA @ 300V		
Fuse Size (Not Supplied)	1/4 x 1-1/4 in.	5 x 20 mm		
Short-Circuit Current Rating	See page 12-43			
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color: Black No-indication	1492-H6	25	1492-WFB4	50
Black w/LED	1492-H5	25	1492-WFB424	50
Black w/Neon	1492-H4	25	1492-WFB4250	50
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails:				
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2
3 ft Scored A-B Rail	1492-N1	20	—	—
3 ft Rigid A-B Rail	1492-N22	20	—	—
3 ft High Rise A-B Rail	1492-N44	2	—	—
Standoff Brackets (Use Every 12 in.)	1492-N25	2	—	—
End Barrier	1492-N37	50	Not Required	—
End Anchors and Retainers:				
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50
A-B Rail — Heavy Duty	1492-N23	10	—	—
Uninsulated 10-Pole Side Jumper	1492-N49	10	1492-SJFB8-10	10
Side Jumper Insulating Sleeve	1492-SJS	10	—	—
Other Accessories:				
Partition Plate	—	—	1492-PPSL3	50
Group Marking Carrier	1492-GM35	25	1492-GM35	25
Marking Systems:				
Snap-In Marker Card — For Base Block	1492-MS8X12 (56/card)	5	1492-MS8X12 (56/card)	5
For Handle	1492-MS8X9 (56/card)	5	1492-MS8X9 (56/card)	5
Adhesive Labels	1492-ALHFB (50/sheet)	1	1492-ALHFB (50/card)	1

* IEC standards for 5 x 20 mm fuses do not include ratings above 6.3 A.