



Screw Connection Terminal Blocks

Fuse Blocks, Continued

1492-JD3FB

1492-JDG3FB

Dimensions are not intended to be used for manufacturing purposes.
Note: Height dimension is measured from top of rail to top of terminal block.



Specifications	Two-level terminal block with feed-through circuit and hinged-arm fuse circuit			Three-Level terminal block with feed-through circuit, hinged-arm fuse circuit, and ground point		
Certifications	UL	CSA	IEC	UL	CSA	IEC
Voltage Rating	300V AC/DC		500V AC/DC	300V AC/DC		500V AC/DC
Maximum Fuse Circuit Current	10 A	10 A/250V	6.3 A*	10 A	10 A/250V	6.3 A*
Maximum Feed-through Circuit Current	20 A	25 A		20 A	25 A	
Wire Range (Rated Cross Section)	#22...12 AWG	#26...12 AWG	0.5...4 mm ²	#22...12 AWG	#26...12 AWG	0.5...4 mm ²
Fuse Size (Not Supplied)	5 x 20 mm			5 x 20 mm		
Wire Strip Length	0.35 in. (9 mm)			0.35 in. (9 mm)		
Recommended Tightening Torque	5.5 lb•in. (0.6 N•m)			5.5 lb•in. (0.6 N•m)		
Density	38 pcs/ft (125 pcs/m)			38 pcs/ft (125 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
Short-Circuit Current Rating	See page 12-43					

Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color: Grey	1492-JD3FB	50	1492-JDG3FB	50
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails:				
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2
End Barrier Grey	1492-EBJD3FB	20	1492-EBJD3FB	20
End Anchors:				
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20
DIN Rail - Normal Duty	1492-EAJ35	100	1492-EAJ35	100
DIN Rail - Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50
Jumpers:				
Side Jumper — 4-pole	1492-SJ8A-4	50	1492-SJ8A-4	50
Side Jumper — 3-pole	1492-SJ8A-3	50	1492-SJ8A-3	50
Side Jumper — 2-pole	1492-SJ8A-2	50	1492-SJ8A-2	50
Group Marking				
Rail Mount Group Marking Carrier	1492-GM35	25	1492-GM35	25
End Anchor Top Marker Carrier*	1492-GMC	50	1492-GMC	50
Cat. No. 1492-GMC Top Marker Tag	1492-M5X30 (20/card)	5	1492-M5X30 (20/card)	5
Marking Systems:				
Snap-in marker cards (Handle)	1492-M7X12 (108/card)	5	1492-M7X12 (108/card)	5
Snap-in marker cards (Handle)	1492-MR6X8 (120/card)	5	1492-MR6X8 (120/card)	5
Snap-in marker cards (Side)	1492-M6X5 (200/card)	5	1492-M6X5 (200/card)	5

* IEC standards for 5 x 20 mm fuses do not include ratings above 6.3 A.

* The Bulletin 1492-GMC marker carrier installs directly on the top of a 1492-EAJ35 end anchor or a 1492-ERL35 end retainer for group marking purposes.