


Spring-Clamp Connection Terminal Blocks

Isolation Blocks

1492-LKD3

Dimensions are not intended to be used for manufacturing purposes.

Note: Height dimension is measured from top of rail to top of terminal block.



Specifications	<i>Knife Disconnect Feed-through Terminal Block</i>		
Certifications		CSA	IEC
Voltage Rating	600V AC/DC	500V AC/DC	
Maximum Current	20 A	24 A	
Wire Range (Rated Cross Section)	#30...12 AWG	2.5 mm ²	
Wire Strip Length	0.39 in. (10 mm)		
Density	59 pcs/ft (196 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)		
Terminal Blocks	Cat. No.	Pkg Qty.	
Color	Grey	1492-LKD3	25
Accessories	Cat. No.	Pkg Qty.	
Mounting Rails			
1 m Symmetrical DIN (Steel)	199-DR1	10	
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	
End Barriers	Grey	1492-EBL3	50
End Anchors and Retainers			
Screwless End Retainer	1492-ERL35	20	
DIN Rail — Normal Duty	1492-EAJ35	100	
DIN Rail — Heavy Duty	1492-EAHJ35	50	
Jumpers			
Plug-in Center Jumper — 50-Pole	1492-CJK5-50	10	
Plug-in Center Jumper — 10-Pole	1492-CJK5-10	20	
Plug-in Center Jumper — 9-Pole	1492-CJK5-9	20	
Plug-in Center Jumper — 8-Pole	1492-CJK5-8	20	
Plug-in Center Jumper — 7-Pole	1492-CJK5-7	20	
Plug-in Center Jumper — 6-Pole	1492-CJK5-6	20	
Plug-in Center Jumper — 5-Pole	1492-CJK5-5	20	
Plug-in Center Jumper — 4-Pole	1492-CJK5-4	60	
Plug-in Center Jumper — 3-Pole	1492-CJK5-3	60	
Plug-in Center Jumper — 2-Pole	1492-CJK5-2	60	
Other Accessories			
Reducing Sleeves 28...24 AWG (0.13...0.2 mm ²) White	1492-PSL3-2	100	
Reducing Sleeves 22...20 AWG (0.25...0.5 mm ²) Grey	1492-PSL3-5	100	
Reducing Sleeves 18 AWG (0.75...1.0 mm ²) Dark Grey	1492-PSL3-10	100	
Test Plug	1492-TP23	20	
Test Plug (Stackable)	1492-TPL5	25	
Electrical Warning Plate	1492-EWPL5	20	
Group Marking Carrier	1492-GM35	25	
Marking Systems			
Snap-In Marker Cards	1492-M5X10 (144/card)	5	
Snap-In Marker Cards	1492-M5X5 (200/card)	5	