




Screw Connection Terminal Blocks

Plug-In Style Terminal Blocks

	1492-J3P			1492-J3PTP			1492-JD3P		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.									
Specifications	Selectable component plug-in terminal block			Selectable component plug-in terminal block with test plug socket			Two Circuit selectable component plug-in terminal block		
Certifications		CSA	IEC		CSA	IEC		CSA	IEC
Voltage Rating	600V AC/DC	300V AC/DC	500V AC/DC	300V AC/DC		500V AC/DC	300V AC/DC		500V AC/DC
Maximum Current	20 A	10 A	24 A	20 A	10 A	24 A	20 A		24 A
Wire Range (Rated Cross Section)	#30...12 AWG		2.5 mm ²	#30...12 AWG		2.5 mm ²	#24...12 AWG	#30...12 AWG	2.5 mm ²
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)			0.31 in. (8 mm)		
Recommended Tightening Torque	4.4 lb•in (0.5 N•m)			4.4 lb•in (0.5 N•m)			4.4 lb•in (0.5 N•m)		
Density	59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
Short-Circuit Current Rating	See page 12-42								
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Color:	Grey	1492-J3P	100	1492-J3PTP	100		1492-JD3P	50	
	Red	1492-J3P-RE	100	—	—	—	—	—	—
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Mounting Rails:									
1 m Symmetrical DIN (Steel)		199-DR1	10	199-DR1	10	199-DR1	10	199-DR1	10
1 m Symmetrical DIN (Aluminum)		1492-DR5	10	1492-DR5	10	1492-DR5	10	1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2	1492-DR6	2	1492-DR6	2	1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2	1492-DR7	2	1492-DR7	2	1492-DR7	2
End Barriers		1492-EBJ3	50	1492-EBJ3	50	1492-EBJD3P	20		
End Anchors and Retainers:									
Screwless End Retainer		1492-ERL35	20	1492-ERL35	20	1492-ERL35	20		
DIN Rail — Normal Duty		1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100		
DIN Rail — Heavy Duty		1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50		
Jumpers* †:									
Center Jumper — 50-Pole		1492-CJLJ5-50	10	1492-CJLJ5-50	10	—	—	—	—
Center Jumper — 10-Pole		1492-CJLJ5-10	20	1492-CJLJ5-10	20	1492-CJJ5-10	20		
Center Jumper — 9-Pole		1492-CJLJ5-9	20	1492-CJLJ5-9	20	—	—		
Center Jumper — 8-Pole		1492-CJLJ5-8	20	1492-CJLJ5-8	20	—	—		
Center Jumper — 7-Pole		1492-CJLJ5-7	20	1492-CJLJ5-7	20	—	—		
Center Jumper — 6-Pole		1492-CJLJ5-6	20	1492-CJLJ5-6	20	—	—		
Center Jumper — 5-Pole		1492-CJLJ5-5	20	1492-CJLJ5-5	20	—	—		
Center Jumper — 4-Pole		1492-CJLJ5-4	60	1492-CJLJ5-4	60	1492-CJJ5-4	50		
Center Jumper — 3-Pole		1492-CJLJ5-3	60	1492-CJLJ5-3	60	1492-CJJ5-3	50		
Center Jumper — 2-Pole		1492-CJLJ5-2	60	1492-CJLJ5-2	60	1492-CJJ5-2	50		
Screw Type Jumper Notching Tool		—	—	—	—	1492-T1	1		
Other Accessories:									
Partition Plate		1492-EBJ16	20	1492-EBJ16	20	1492-PPJD3P	20		
Test Plug		—	—	1492-TP23	20	—	—		
Disconnect Plug		1492-DPL	50	1492-DPL	50	1492-DPL	50		
Component Plug		1492-CPL	50	1492-CPL	50	1492-CPL	50		
Fuse Plug									
Without Blown Fuse Indicator		1492-FPK2	20	1492-FPK2	20	1492-FPK2	20		
10...36V Blown Fuse Indicator		1492-FPK224	20	1492-FPK224	20	1492-FPK224	20		
35...70V Blown Fuse Indicator		1492-FPK248	20	1492-FPK248	20	1492-FPK248	20		
60...150V Blown Fuse Indicator		1492-FPK2120	20	1492-FPK2120	20	1492-FPK2120	20		
140...250V Blown Fuse Indicator		1492-FPK2250	20	1492-FPK2250	20	1492-FPK2250	20		
Marking Systems:									
Snap-in marker cards		1492-M5X12 (144/card)	5	1492-M5X12 (144/card)	5	1492-SM5X10 (144/card)	5		
Snap-in marker cards		1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5		

* Cat. nos. 1492-J3P and J3PTP use screwless center jumpers. Cat. No. 1492-JD3P uses a screw-type center jumper.

† Use of Center Jumpers may affect spacings, requiring derating of terminal blocks. See the Terminal Block selection guide, pub. no. 1492-SG008*.

