

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks, Continued

	1492-L16			1492-L16D*			1492-L35					
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.												
	Specifications <i>Feed-through Terminal Block</i>			Specifications <i>Power Distribution Block with Center Jumper Connection/Feed</i>			Specifications <i>Feed-through Terminal Block</i>					
Certifications		CSA	IEC	ATEX		CSA	IEC		CSA	IEC	ATEX	
Voltage Rating	600V AC/DC			800V AC/DC	550V AC/DC	600V AC/DC		500V AC/DC	600V AC/DC			
Maximum Current	65 A			76 A	66 A	65 A		76 A	120 A			
Wire Range (Rated Cross Section)	#14...4 AWG			16 mm ²	(16...6 AWG)	#14...4 AWG		16 mm ²	#12...2 AWG		35 mm ²	
Wire Strip Length	0.70 in. (18 mm)			0.70 in. (18 mm)			0.98 in. (25 mm)					
Density	25 pcs/ft (82 pcs/m)			20 pcs/ft (66 pcs/m)			18 pcs/ft (62 pcs/m)					
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)					
Short-Circuit Current Rating	See page 12-71											
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Color	Grey	1492-L16	25		1492-L16D*	20		1492-L35	10			
	Red	1492-L16-RE	25		—	—		1492-L35-RE	10			
	Blue	1492-L16-B	25		—	—		1492-L35-B	10			
	Black	1492-L16-BL	25		—	—		1492-L35-BL	10			
	Green	1492-L16-G	25		—	—		1492-L35-G	10			
	Yellow	1492-L16-Y	25		—	—		1492-L35-Y	10			
	Orange	1492-L16-OR	25		—	—		1492-L35-OR	10			
	Brown	1492-L16-BR	25		—	—		1492-L35-BR	10			
	White	1492-L16-W	25		—	—		1492-L35-W	10			
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Mounting Rails												
1 m Symmetrical DIN (Steel)		199-DR1	10		199-DR1	10		199-DR1	10			
1 m Symmetrical Heavy Duty DIN (Steel, Unslotted)		199-DR4	5		199-DR4	5		199-DR4	5			
1 m Symmetrical DIN (Aluminum)		1492-DR5	10		1492-DR5	10		1492-DR5	10			
1 m Hi-Rise Symmetrical DIN (Aluminum)		1492-DR6	2		1492-DR6	2		1492-DR6	2			
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2		1492-DR7	2		1492-DR7	2			
1 m Symmetrical Heavy Duty DIN (Copper, Unslotted)		1492-DR8	5		1492-DR8	5		1492-DR8	5			
1 m Symmetrical Heavy Duty DIN (Steel Slotted)		1492-DR9	5		1492-DR9	5		1492-DR9	5			
End Barriers	Grey	1492-EBL16	20		Integrated to Block	—		Integrated to Block	—			
	Blue	1492-EBL16-B	20		—	—		—	—			
	Yellow	1492-EBL16-Y	20		—	—		—	—			
End Anchors and Retainers												
Screwless End Retainer		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20			
DIN Rail — Normal Duty		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100			
DIN Rail — Heavy Duty		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50			
Jumpers												
Plug-in Center Jumper — 2-Pole		1492-CJL12-2	25		⚡	—		1492-CJL16-2	10			
Other Accessories												
Test Plug		1492-TP23	20		1492-TP23	20		1492-TP23	20			
Test Adapter		—	—		—	—		—	—			
Electrical Warning Plate		1492-EWPL12	20		1492-EWPL12	20		1492-EWPL16	20			
Group Marking Carrier		1492-GM35	25		1492-GM35	25		1492-GM35	25			
Marking Systems												
Snap-In Marker Cards‡		1492-M7X12 (108/card)	5		1492-M7X12 (108/card)	5		1492-M7X12 (108/card)	5			
Snap-In Marker Cards		1492-M8X5 (160/card)	5		1492-M8X5 (160/card)	5		1492-M8X5 (160/card)	5			
Hinged Marker Cards		1492-MH5X15 (96/card)	5		1492-MH5X15 (96/card)	5		1492-MH5X15 (96/card)	5			

* Can be electrically connected through center jumper for power distribution to 1492 - L3, L3Q, L4, L4T, L4Q, L6, and L6T terminal blocks. See page 12-53 for distribution guidelines.

⚡ Use defined center jumper for standard terminal blocks when connecting for power distribution.

‡ May only be mounted in terminal block corner marking positions.