

# Screw Connection Terminal Blocks

## Mini Blocks

	1492-WM3				1492-WM4				1492-WMD1		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.											
	<b>Specifications</b>				<i>Single-circuit mini terminal block.</i>				<i>Two-circuit mini terminal block.</i>		
<b>Certifications</b>											
<b>Voltage Rating</b>	300V AC/DC	500V AC/DC	300V AC/DC	420V AC/DC	300V AC/DC	500V AC/DC	300V AC/DC	420V AC/DC	300V AC/DC	300V AC/DC	500V AC/DC
<b>Maximum Current</b>	15 A	24 A	15 A	24 A	20 A	32 A	20 A	32 A	15 A	15 A	17.5 A
<b>Wire Range (Rated Cross Section)</b>	#30...14 AWG	0.5...2.5 mm <sup>2</sup>	#22...14 AWG	2.5 mm <sup>2</sup>	#22...12 AWG	0.5...4.0 mm <sup>2</sup>	#22...12 AWG	4.0 mm <sup>2</sup>	#22...16 AWG	0.5...1.5 mm <sup>2</sup>	
<b>Wire Strip Length</b>	0.24 in. (6 mm)				0.39 in. (10 mm)				0.35 in (9 mm)		
<b>Recommended Tightening Torque</b>	4.2...4.6 lb•in. (0.5 N•m)				5.0...5.6 lb•in. (0.6 N•m)				4.2...4.6 lb•in (0.5 N•m)		
<b>Density</b>	61 pcs/ft (200/m)				50 pcs/ft (166/m)				61 pcs/ft (200/m)		
<b>Housing Temperature Range</b>	-40...+195 °F (-40...+90 °C)				-40...+195 °F (-40...+90 °C)				-40...+195 °F (-40...+90 °C)		
<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	
<b>Color:</b>	Grey	<b>1492-WM3</b>	50	<b>1492-WM4</b>	50	<b>1492-WMD1</b>	50	<b>1492-WMD1-RE</b>	50		
	Red	<b>1492-WM3-RE</b>	50	<b>1492-WM4-RE</b>	50	<b>1492-WMD1-B</b>	50	<b>1492-WMD1-G</b>	50		
	Blue	<b>1492-WM3-B</b>	50	<b>1492-WM4-B</b>	50	<b>1492-WMD1-Y</b>	50	<b>1492-WMD1-OR</b>	50		
	Black	<b>1492-WM3-BL</b>	50	<b>1492-WM4-BL</b>	50	<b>1492-WMD1-W</b>	50				
	Green	<b>1492-WM3-G</b>	50	<b>1492-WM4-G</b>	50						
	Yellow	<b>1492-WM3-Y</b>	50	<b>1492-WM4-Y</b>	50						
	Orange	<b>1492-WM3-OR</b>	50	<b>1492-WM4-OR</b>	50						
	Brown	<b>1492-WM3-BR</b>	50	<b>1492-WM4-BR</b>	50						
	White	<b>1492-WM3-W</b>	50	<b>1492-WM4-W</b>	50						
<b>Accessories</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>			
<b>Mounting Rails:</b> 1 m Sym. mini DIN (Steel)	<b>1492-DR3</b>	5	<b>1492-DR3</b>	5	<b>1492-DR3</b>	5					
<b>End Barrier</b>	<b>1492-EBM3</b>	50	<b>1492-EBM4</b>	50	<b>1492-EBMD1</b>	50					
<b>End Anchors and Retainers:</b> Mini Screwless End Retainer	<b>1492-ERL15</b>	20	<b>1492-ERL15</b>	20	<b>1492-ERL15</b>	20					
<b>Mini DIN Anchor — Normal Duty</b>	<b>1492-EAJ15</b>	50	<b>1492-EAJ15</b>	50	<b>1492-EAJ15</b>	50					
<b>Jumpers:</b> Insulated Side Jumper	<b>1492-SJM5-10 (10-pole)</b>	10	<b>1492-N42 (2-pole)</b> <b>1492-SJ6-10 (10-pole)</b>	50 10							
Side Jumper — 12-pole insulated	—	—	—	—	<b>1492-SJMD5-12 (Uninsulated)</b>	10					
Center Jumper — 50-pole	—	—	<b>1492-CJD6-50</b>	5							
Center Jumper — 10-pole	<b>1492-CJM5-10</b>	10	<b>1492-CJD6-10</b>	10							
Center Jumper — 5-pole	—	—	<b>1492-CJD6-5</b>	10							
Center Jumper — 4-pole	—	—	<b>1492-CJD6-4</b>	10							
Center Jumper — 3-pole	<b>1492-CJM5-3</b>	10	<b>1492-CJD6-3</b>	10							
Center Jumper — 2-pole	<b>1492-CJM5-2</b>	10	<b>1492-CJD6-2</b>	10							
Center Jumper Link	<b>1492-CJL5</b>	10	<b>1492-CJL6</b>	10							
<b>Other Accessories:</b> Partition Plate	<b>1492-PPM3</b>	50	<b>1492-PPM3</b>	50	<b>1492-PPMD1</b>	50					
Test Plug	—	—	<b>1492-TP28</b>	10							
Test Plug Adapter	<b>1492-TA285</b>	10	<b>1492-TA40</b>	10							
Electrical Warning Plate (4-pole)	—	—	<b>1492-EWP6-4</b>	10							
<b>Marking Systems:</b> Snap-in Marker Card	<b>1492-MS5X5 (80/card)</b>	5	<b>1492-MS6X9 (80/card)</b>	5	<b>1492-MS5X5 (80/card)</b>	5					
Individual Marker Tab (single character)*	<b>1492-MP5(100/card)</b>	5	<b>1492-MP(10/stick)</b>	10	<b>1492-MP5(100/card)</b>	5					

\* Cat. no. is incomplete. See page 12-82.