


# Spring-Clamp Connection Terminal Blocks

## Single-Circuit Automotive Fuse Block

### 1492-LAFB6

Dimensions are not intended to be used for manufacturing purposes.  
**Note:** Height dimension is measured from top of rail to top of terminal block.



Specifications		Single-circuit automotive style fuse terminal block with or without LED blown fuse indication		
Certifications		<b>UL</b>	<b>CSA</b>	<b>IEC</b>
Voltage Rating	-LAFB6	300V AC/DC		250V AC/DC
	-LAFB624	10...36V AC/DC		
Maximum Current		30 A	25 A	30 A
Wire Range (Rated Cross Section)		#22...12 AWG	#22...10 AWG	0.5...6 mm <sup>2</sup>
Wire Strip Length		0.394 in. (10 mm)		
Density		37 pcs/ft (123 pcs/m)		
Housing Temperature Range		-58...+248 °F (-50...+120 °C)		
Terminal Blocks		Cat. No.		Pkg Qty.
Color	Black (without blown fuse indication)	1492-LAFB6		25
	Black (with blown fuse indication)	<b>1492-LAFB624</b>		25
Accessories		Cat. No.		Pkg Qty.
Mounting Rails				
1 m Symmetrical DIN (Steel)		<b>199-DR1</b>		10
1 m Symmetrical DIN (Aluminum)		<b>1492-DR5</b>		10
1 m Hi-Rise Sym. DIN (Aluminum)		<b>1492-DR6</b>		2
1 m Angled Hi-Rise Sym. DIN (Steel)		<b>1492-DR7</b>		2
End Barrier	Black	<b>1492-EBLAFB6</b>		50
End Anchors		<b>1492-ERL35</b>		20
Screwless End Retainer				
DIN Rail - Normal Duty		<b>1492-EAJ35</b>		100
Din Rail - Heavy Duty		<b>1492-EAHJ35</b>		50
Jumpers				
Plug-in Center Jumper — 32-Pole		<b>1492-CJL8-32</b>		10
Plug-in Center Jumper — 4-Pole		<b>1492-CJL8-4</b>		60
Plug-in Center Jumper — 3-Pole		<b>1492-CJL8-3</b>		60
Plug-in Center Jumper — 2-Pole		<b>1492-CJL8-2</b>		60
Test Adapter		1492-TPL8		25
Marking Systems				
Snap-in Marker Cards		<b>1492-M5X8</b> (144/card)		5
Snap-In Marker Cards		<b>1492-M6X5</b> (200/card)		5