

Spring-Clamp Connection Terminal Blocks

Fuse Blocks

		1492-RFB4...			1492-RAFB4...		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.							
Specifications		Single-circuit fuse terminal block with or without blown fuse indicator			Single-circuit fuse terminal block with or without blown fuse indicator		
Certifications			cUR	IEC		cUR	IEC
Maximum Current		15 A*	15 A*	15 A*	12 A	12 A	12 A
Wire Range (Rated Cross Section)		#22...12 AWG	#22...12 AWG	0.5...4 mm ²	#22...12 AWG	#22...12 AWG	0.5...4 mm ²
Voltage Rating		RFB4/RAFB4	300V AC/DC	500V AC/DC	300V AC/DC	500V AC/DC	
		RFB424/RAFB424	10...57V AC/DC		10...57V AC/DC		
		RFB4250/RAFB4250	85...264V AC		85...264V AC		
Indicator Type		RFB4/RAFB4	Non-indicating		Non-indicating		
		RFB424/RAFB424	LED		LED		
		RFB4250/RAFB4250	Neon		Neon		
Leakage Current		RFB4/RAFB4	—		—		
		RFB424/RAFB424	2 mA @ 24V		2 mA @ 24V		
		RFB4250/RAFB4250	1 mA @ 264V		1 mA @ 264V		
Fuse Size (Not Supplied)		5 x 20 mm			1/4 x 1 -1/4 in.		
Wire Strip Length		0.47 in. (12 mm)			0.47 in. (12 mm)		
Density		37 pcs/ft (125 pcs/m)			30 pcs/ft (100 pcs/m)		
Insulation Temperature Range		-4...+140 °F (-20...+60 °C)			-4...+221 °F (-40...+105 °C)		
Terminal Blocks		Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color	Black (Non-Indicating)	1492-RFB4	25	1492-RAFB4	25	1492-RAFB4	25
	Black (10...57V LED)	1492-RFB424	25	1492-RAFB424	25	1492-RAFB424	25
	Black (85...264V Neon)	1492-RFB4250	25	1492-RAFB4250	25	1492-RAFB4250	25
Accessories		Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails							
	1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10
	1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10
	1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2
	1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2
End Barrier		Not Required	—	Not Required	—	Not Required	—
End Retainers/Anchors							
	Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20
	DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50
	Plug-in Center Jumper, 10-Pole	1492-CJR8-10	10	—	—	—	—
	Plug-in Center Jumper, 9-Pole	1492-CJR8-9	10	—	—	—	—
	Plug-in Center Jumper, 8-Pole	1492-CJR8-8	10	—	—	—	—
	Plug-in Center Jumper, 7-Pole	1492-CJR8-7	10	—	—	—	—
	Plug-in Center Jumper, 6-Pole	1492-CJR8-6	10	—	—	—	—
	Plug-in Center Jumper, 5-Pole	1492-CJR8-5	10	1492-CJRA10-5	10	1492-CJRA10-5	10
	Plug-in Center Jumper, 4-Pole	1492-CJR8-4	10	1492-CJRA10-4	10	1492-CJRA10-4	10
	Plug-in Center Jumper, 3-Pole	1492-CJR8-3	10	1492-CJRA10-3	10	1492-CJRA10-3	10
	Plug-in Center Jumper, 2-Pole	1492-CJR8-2	10	1492-CJRA10-2	10	1492-CJRA10-2	10
Center Jumper Link		1492-CJRL6	10	1492-CJRL5	10	1492-CJRL5	10
Other Accessories							
Accessories Group	Mounting Rails: Partition Plate	1492-GM35	25	1492-GM35	25	1492-GM35	25
Marking Carrier							
Marking Systems							
	Snap-in Marker for Block	1492-MS8X12 (56/card)	5	1492-MS8X12 (56/card)	5	1492-MS8X12 (56/card)	5
	Snap-in Marker for Handle	1492-MS6X9 (80/card)	5	1492-MS6X9 (80/card)	5	1492-MS6X9 (80/card)	5

* IEC standards for 5 x 20 mm fuses do not include ratings above 6.3 A.