


# Screw Connection Terminal Blocks

## Space-Saver Grounding Blocks, Continued

### 1492-WG16S

Dimensions are not intended to be used for manufacturing purposes.

**Note:** Height dimension is measured from top of rail to top of terminal block.



<b>Specifications</b>	<i>Single-circuit grounding terminal block.</i>		
Certifications		<b>CSA</b>	<b>IEC</b>
Voltage Rating	—		
Maximum Current	Grounding		
Wire Range (Rated Cross Section)	#14...4 AWG	2.5...16 mm <sup>2</sup>	
Wire Strip Length	0.51 in. (13 mm)		
Recommended Tightening Torque	18...20 lb•in. (2.1 N•m)		
Center Screw Mounting Torque	10.6 lb•in. (1.2 N•m)		
Density	27 pcs/ft (90 pcs/m)		
Housing Temperature Range	-40...+195 °F (-40...+90 °C)		

<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>
Color: Green/Yellow	<b>1492-WG16S</b>	25
<b>Accessories</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>
Mounting Rails:		
1 m Symmetrical DIN (Steel)	<b>199-DR1</b>	10
1 m Symmetrical DIN (Aluminum)	<b>1492-DR5</b>	10
1 m Hi-Rise Sym. DIN (Aluminum)	<b>1492-DR6</b>	2
1 m Angled Hi-Rise Sym. DIN (Steel)	<b>1492-DR7</b>	2
1 m Symmetrical DIN (Copper)	<b>1492-DR8</b>	5
1 m Symmetrical DIN (Steel)	<b>1492-DR9</b>	5
End Barrier	Not Required	—
End Anchors:		
DIN Rail — Normal Duty	<b>1492-EAJ35</b>	100
DIN Rail — Heavy Duty	<b>1492-EAHJ35</b>	50
Other Accessories:		
Group Marking Carrier	<b>1492-GM35</b>	25
Marking Systems:		
Snap-in Marker Card	<b>1492-MS6X12 (80/card)</b>	5