

COMMON TOLERANCE		QUALITY	<6	>6	>30	>120	>315	>1000	>2000	>4000	SHORT SIDE	>3	>6	>30	>120	NOTE: - ACCURATE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT	CONFIDENTIAL - PROPRIETARY
		COARSE	0.2	0.5	0.8	1.2	2	3	4	5		<6	<30	<120	>120		
		MEDIUM	0.1	0.2	0.3	0.5	0.8	1.2	2	3	ANGULAR COMMON TOLERANCE	1°	30'	20'	10'		
		ACCURATE	0.05	0.1	0.15	0.2	0.3	0.5									