

COMMON TOLERANCE		QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤4000	>4000	SHORT SIDE	<3 ≥6	>3 ≤30	>30 ≤120	>120	NOTE: - ACCURATE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT	CONFIDENTIAL - PROPRIETARY *THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEMI AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION*									
		COARSE	0.2	0.5	0.8	1.2	2	3	4		5	ANGULAR COMMON TOLERANCE	1 ±	30 ′		20 ′	10 ′								
		MEDIUM	0.1	0.2	0.3	0.5	0.8	1.2	2		3														
		ACCURATE	0.05	0.1	0.15	0.2	0.3	0.5																	

