

PRODUCT PROFILE

1791ES CompactBlock™ Guard I/O™

Improve productivity; simplify control system design, while enhancing operator protection

Benefits

- I/O point level diagnostics and LEDs: quickly identify a problem and help reduce machine downtime
- TÜV certified: for use in safety applications, up to SIL3 and CAT 4
- Versatility: can connect to both standard and safety-rated sensors
- Easy Configuration: via RSLogix™
 5000 with full support of IP addressing
- Flexibility: supports connection of single and dual channel safety devices on inputs and outputs
- Individual Test Outputs: An individual test output can be assigned for each safety input device, allowing for optimized cable installations.
- Muting Lamp control: provided on selected test pulse outputs for lamp control and fault monitoring
- **Standard control:** use test outputs for panel lamps, standard actuators, etc.
- Compatibilty EtherNet/IP is standard Ethernet and can be used with standard media i.e. fiber, wireless, etc.



CompactBlock™ Guard I/O™ on EtherNet/IP is a safety rated I/O module designed for use in safety applications. It communicates on EtherNet/IP using the CIP Safety protocol and is optimized to work with GuardLogix® controllers.

The application of the CIP Safety protocol enables the simultaneous transmission of safety and standard control data and diagnostics information over a common EtherNet/IP network. EtherNet/IP enables a flat network topology by reducing the number of networks for different control disciplines and also by allowing standard and safe control on the same network.

CompactBlock Guard I/O on EtherNet/IP is ideal for applications where Ethernet technology is preferred or for applications requiring highly distributed I/O blocks close to sensors and actuators. The compact footprint and solid-state design allows for module replacement in minutes and reduces the need for special maintenance or training.

CompactBlock Guard I/O is designed for use with industrial equipment and is especially suited for robotic, point-of operation, guard-monitoring and distributed control applications covering long distances.



PRODUCT SPECIFICATIONS

Cat. No.	1791ES-IB16	1791ES-IB8XOBV4
Description	24V dc Input Module on Ethernet/IP Networks	24V dc Input/Solid-State Output Module on Ethernet/IP Networks
Eurrent Consumption	250 mA @ 24V dc	250 mA @ 24V dc
Operating Voltage Range	19.2 28.8V dc (24V dc, -20 +20%)	19.2 28.8V dc (24V dc, -20 +20%)
/O Channel Isolation	Isolated	Isolated
Digital Inputs		
lumber of Inputs (single-channel)	16 safety	8 safety
oltage, On-State Input, Min.	11 V dc	11 V dc
oltage, Off-State Input, Max.	5V dc	5V dc
urrent, On-State Input, Min.	3.3 mA	3.3 mA
nput Delay Time, OFF to ON	16.2 ms max	16.2 ms max
nput Delay Time, ON to OFF	16.2 ms max	16.2 ms max
Digital Outputs		
Number of Outputs	_	4 dual channel Bipolar
Output Type	_	current sourcing/current sinking pair
Output Current Rating		2 A max. per point 8 A total module @ 40 °C (104 °F) 6 A total module @ 60 °C (140 °F)
Output Leakage Current, Max.	_	± 1.0 mA
lutput Delay Time, OFF to ON, Max.	_	6.2 ms
Output Delay Time, ON to OFF, Max.	_	6.2 ms
hort Circuit Protection	_	Yes
Overcurrent Detection	_	Yes
tandard Pulse Test Outputs		
lumber of Pulse Test Sources	16	8
Pulse Test Output Current	0.7 A per point	0.7 A per point
Pulse Test Output Leakage Current, Max.	0.1 mA	0.1 mA
hort Circuit Protection	Yes	Yes
Overcurrent Protection	Yes	Yes
ieneral		
)perating Temperature	-20°C+60°C (-4°F+140°F)	-20°C+60°C (-4°F+140°F)
itorage Temperature	-40°C+85°C (-40°F+185°F)	-40°C+85°C (-40°F+185°F)
Relative Humidity	595% noncondensing	595% noncondensing
/ibration	5 g @ 10500 Hz	5 g @ 10500 Hz
Shock, Operating	30 g	30 g
Enclosure Protection	IP 20	IP 20
Dimensions (HxWxD), Metric	80 x 196 x 77 mm ¹	80 x 196 x 77 mm ¹
Dimensions (HxWxD), Imperial	3.2 x 7.7 x 3 in ¹	3.2 x 7.7 x3 in ¹
Weight, Metric	600 g	600 g
Weight, Imperial	1.32 lb	1.32 lb

¹ Includes DIN latch and connectors.

www.rockwellautomation.com

Power, Control and Information Solutions Headquarters

Americas: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444
Europe/Middle East/Africa: Rockwell Automation, Vorstlaan/Boulevard du Souverain 36, 1170 Brussels, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640
Asia Pacific: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846

³ When product is marked. See the Product Certification link at http://www.ab.com/certification for Declarations of Conformity, Certificates, and other certification details. All specifications are subject to change. Refer to product installations instructions.