








CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	



NOT QUOTED BEVELS	/	MATERIAL	/	TREATMENT	/
-------------------	---	----------	---	-----------	---

MOD. N°	DATE	SIGN.	REPLACES	DATE	SIGN.
SIGNATURE	DATE	SIGN.	REPLACED BY	DATE	SIGN.

1st DRAW	DESIGN	CHECKED	TOLERANCE	SCALE	UNIT	SHEET
25.08.21	ROMANO	25.08.21	MEDIUM	/	MM	1 OF 3









TITLE	DIMA VK3500 24.0" /BA VESA	RELEASE	A	LEVEL	00
DRAWING N°	DIMA_VK3500_240BA_VESA				

CONFIDENTIAL-PROPRIETARY

THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION.

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COMMON TOLERANCE	COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4
	MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2
	ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	



CONFIDENTIAL—PROPRIETARY

"THIS DRAWING AND SPECIFICATIONS, HEREIN, ARE THE PROPERTY OF ASEM SpA AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION."

SHORT SIDE	>3 ≤6	>6 ≤30	>30 ≤120	>120
ANGULAR COMMON TOLERANCE	±1°	±30'	±20'	±10'

QUALITY	<6	>6 ≤30	>30 ≤120	>120 ≤315	>315 ≤1000	>1000 ≤2000	>2000 ≤4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5		

