


CONFIDENTIAL - PROPRIETARY
THIS DRAWING IS THE PROPERTY OF ASEMI, INC. AND IS NOT TO BE REPRODUCED OR COPIED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF ASEMI, INC.

NOTE:
- ACCURATE TRIM REQUESTED
- BENDING RADIUS MINIMUM POSSIBLE
- BENDING RADIUS MAXIMUM POSSIBLE
- THE DIMENSIONS INCLUDING THE TREATMENT
- THE DIMENSIONS INCLUDING THE TREATMENT

SHORT SIDE	>3	>6	>30	>120
COMMON	<3	<6	<30	<120
ANGULAR TOLERANCE	1°	30'	20'	10'

QUALITY	>30	>120	>315	>1000	>2000	>4000
COMMON	<30	<120	<315	<1000	<2000	<4000
COARSE	0.2	0.5	0.8	1.2	2	3
MEDIUM	0.1	0.2	0.3	0.5	0.8	1.2
ACCURATE	0.05	0.1	0.15	0.2	0.3	0.5

COMMON TOLERANCE	QUALITY	DATE	DESIGN	CHECKED	TOLERANCE	SCALE	UNIT	SHEET	OF
COMMON	0.2	0.5	0.8	1.2	2	3	4	5	6
COARSE	0.1	0.2	0.3	0.5	0.8	1.2	2	3	4
MEDIUM	0.05	0.1	0.15	0.2	0.3	0.5	0.8	1.2	2
ACCURATE	0.025	0.05	0.075	0.1	0.15	0.2	0.3	0.5	0.75



MATERIAL	THICKNESS	MODIFICATION N°	DATE
TREATMENT	mm		SIGNATURE
ASEMI		MEDIUM	SCALE 2:5
DATE 09/04/2021	NOT QUOTED BEVELS 2x45°	UNIT mm	SHEET 1 of 1
SIGNATURE Di Doi	NOT QUOTED RADIUS R2		
TITLE MQ200 18.5\"W TFK			
DRAWING N° D09201925		RELEASE A	LEVEL 00
		SIZE A2	