



- NOTES:
 1. BOX CAN ONLY BE ROTATED CLOCKWISE UP TO 270° FROM ITS ORIGINAL POSITION.
 2. NAMEPLATE TO BE READ FROM CONDUIT BOX SIDE OF MOTOR.
 3. BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180°.

284/86TS	26.47	---	13.00	11.00	9.50	5.50
FRAME	C	AG	B	2F	2XF	BS
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK. ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED. THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT.						
NO.		REVISION		BY & DATE		CHK
3	REDREW DRAWING WAS SAVED WRONG	RJW	08-23-2005	XX	±.03	
2	REDRAWN ON AUTO-CAD	MSG	10-18-2002	TJB	±.005	
1	NEW DRAWING	MUJ36821	CAH	04-02-2001	BW	±.0005
TOLERANCES UNLESS SPECIFIED: DEC. INCHES X ±.1 XX ±.03 TJB XXX ±.005 BW XXXX ±.0005						
FINISH: ANG ±7.30° CAD FILE: SS311136						
TITLE OUTLINE - TEFC 280TS FR. - BB - STD - 12.50 LAM						
DRAWN DAH 04-02-2001 CHK ML 04-02-2001 APPD BW 04-02-2001 SCALE 1=4 REF FWF PREV SS311136						
SIZE		DRAWING NO.		PAGE		REV.
B		SS311136		OF		3

