


CONFIDENTIAL - PROPRIETARY

THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEMI S.p.A. AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION

NOTE: - ACCURATE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT	>120	>30	>6	>3	SHORT SIDE ANGULAR COMMON TOLERANCE
	≤120	≤30	≤30	≤6	
	'10'	'20'	'30'	'1.2'	

QUALITY	COARSE	MEDIUM	ACCURATE	>30	>1000	>2000	>4000
				≤30	≤2000	≤4000	≤4000
				'0.8'	'2'	'3'	'4'
				'0.5'	'1.2'	'0.8'	'1.2'
				'0.3'	'0.5'	'0.3'	'0.5'
				'0.2'	'0.3'	'0.2'	'0.3'
				'0.1'	'0.15'	'0.1'	'0.15'
				'0.05'	'0.1'	'0.05'	'0.1'

COMMON TOLERANCE							
------------------	--	--	--	--	--	--	--



MATERIAL					THICKNESS mm	MODIFICATION N°		DATE	
TREATMENT								SIGNATURE	
		1st DRAW	DESIGN	CHECKED	TOLERANCE MEDIUM		SCALE 1:5		
	DATE	10/02/2022			NOT QUOTED BEVELS 2x45°		UNIT	SHEET OF	
	SIGNATURE	Dereani			NOT QUOTED RADIUS R2		mm	4 of 9	
TITLE DIMA VK3500 24.0" TOP ARM RESISTIVO CON MANIGLIE									
DRAWING N° 00_d18201910						RELEASE A	LEVEL 00	SIZE A3	

CONFIDENTIAL - PROPRIETARY												*THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEMI S.p.A. AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION*														
COMMON TOLERANCE	QUALITY	<6	>6 <30	>30 <120	>120 <315	>315 <1000	>1000 <2000	>4000	SHORT SIDE	NOTE:				- ACCURATE TRIM REQUESTED												
										- BENDING RADIUS: MINIMUM POSSIBLE				- PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS												
										- THE DIMENSIONS INCLUDING THE TREATMENT																
COMMON TOLERANCE	COARSE	0.2	0.5	0.8	1.2	2	3	4	5	ANGULAR COMMON TOLERANCE	1 ±				30 °				20 °				>10 °			
COMMON TOLERANCE	MEDIUM	0.1	0.2	0.3	0.5	0.8	1.2	2	3	ANGULAR COMMON TOLERANCE																
COMMON TOLERANCE	ACCURATE	0.05	0.1	0.15	0.2	0.3	0.5		ANGULAR COMMON TOLERANCE																	

CONFIDENTIAL - PROPRIETARY

THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEMI S.p.A. AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION

NOTE:
- ACCURATE TRIM REQUESTED
- BENDING RADIUS: MINIMUM POSSIBLE
- PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS
- THE DIMENSIONS INCLUDING THE TREATMENT

SHORT SIDE	>120	>30	<30	>6	<6	>3	<3
ANGULAR COMMON TOLERANCE	'10'	'20'	'30'	'1 ±			

	>4000	>2000	<4000	>1000	<2000	>315	<315	>120	<120	>30	<30	>6	<6
	'5	'4	'2	'3	'1.2	'2	'1.2	'0.5	'0.3	'0.15	'0.1	'0.05	'0.1

QUALITY	COARSE	MEDIUM	ACCURATE
COMMON TOLERANCE			

1	2	3	4	5	6	7	8
---	---	---	---	---	---	---	---

A



B

C






D

E

F



DETAGLIO A



MATERIAL				THICKNESS mm		MODIFICATION N°		DATE	
TREATMENT								SIGNATURE	
			1st DRAW	DESIGN	CHECKED	TOLERANCE MEDIUM		SCALE 1:5	
		DATE	10/02/2022			NOT QUOTED BEVELS 2x45°	UNIT mm	SHEET 6 of 9	
		SIGNATURE	Dereani			NOT QUOTED RADIUS R2			
TITLE DIMA VK3500 24.0" TOP ARM RESISTIVO CON MANIGLIE E VASSOIO PORTA TASTIERA									
DRAWING N° 00_d18201910						RELEASE A		LEVEL 00	SIZE A3