


CONFIDENTIAL - PROPRIETARY

THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEMI S.p.A. AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION

NOTE: - ACCURATE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT		>120	>30	>6	>3	SHORT SIDE
		≤120	≤30	≤30	≤6	ANGULAR COMMON TOLERANCE
		'10'	'20'	'30'	'1.2'	

		>4000	>2000	>1000	>315	>120	>30	>6	<6	QUALITY
		'5'	'4'	'3'	'2'	'1.2'	'0.8'	'0.5'	'0.2'	COARSE
		'3'	'2'	'1.2'	'0.8'	'0.5'	'0.3'	'0.2'	'0.1'	MEDIUM
				'0.5'	'0.3'	'0.2'	'0.15'	'0.1'	'0.05'	ACCURATE


COMMON TOLERANCE	
------------------	--




MATERIAL				THICKNESS	MODIFICATION N°		DATE	
TREATMENT				mm			SIGNATURE	
		1st DRAW	DESIGN	CHECKED	TOLERANCE	SCALE		
	DATE	10/02/2022			MEDIUM	1:5		
	SIGNATURE	Dereani			NOT QUOTED BEVELS	2x45°	UNIT	SHEET OF
TITLE					NOT QUOTED RADIUS	R2	mm	1 of 9
DIMA VK3500 24.0" VESA RESISTIVO CON MANIGLIE								
DRAWING N° 00_d18201910					RELEASE	A	LEVEL	00
					SIZE		A3	

NOTE: - ACCURATE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT		ALL DIMENSIONS IN mm (Max 0.3 mm) ON ALL DIRECTIONS	
SHORT SIDE	>120	>30 ≤120	'10'
ANGULAR COMMON TOLERANCE	>3 ≤6	>6 ≤30 '30'	'1.2'

QUALITY		>4000	
COMMON TOLERANCE	COARSE	0.2	'0.5'
	MEDIUM	0.1	'0.3'
	ACCURATE	0.05	'0.1'




MATERIAL					THICKNESS mm	MODIFICATION N°		DATE	
TREATMENT								SIGNATURE	
		1st DRAW	DESIGN	CHECKED	TOLERANCE MEDIUM		SCALE 1:5		
	DATE	10/02/2022			NOT QUOTED BEVELS 2x45°		UNIT mm	SHEET	OF
	SIGNATURE	Dereani			NOT QUOTED RADIUS R2			2 of 9	
TITLE DIMA VK3500 24.0" VESA RESISTIVO CON MANIGLIA PERIMETRALE									
DRAWING N° 00_d18201910						RELEASE A	LEVEL 00	SIZE A3	

CONFIDENTIAL - PROPRIETARY

THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEMI S.p.A. AND MUST NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION

NOTE: - ACCURATE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT		ALL DIMENSIONS IN mm (Max 0.3 mm) ON ALL DIRECTIONS	
SHORT SIDE	ANGULAR COMMON TOLERANCE	>120	'10'
>30	'20'	<120	'20'
>6	'30'	<6	'1 ±

QUALITY		COMMON TOLERANCE	
COARSE	0.2	MEDIUM	0.1
ACCURATE	0.05		
QUALITY		COMMON TOLERANCE	
COARSE	0.2	MEDIUM	0.1
ACCURATE	0.05		



MATERIAL				THICKNESS	MODIFICATION N°		DATE	
TREATMENT				mm			SIGNATURE	
				1st DRAW	DESIGN	CHECKED	TOLERANCE	SCALE
				DATE	10/02/2022		MEDIUM	1:5
				SIGNATURE	Dereani		NOT QUOTED BEVELS 2x45°	UNIT mm
TITLE							NOT QUOTED RADIUS R2	SHEET OF 3 of 9
DIMA VK3500 24.0" VESA RESISTIVO CON MANIGLIE E VASSOIO PORTA TASTIERA								
DRAWING N° 00_d18201910							RELEASE A	LEVEL 00
							SIZE A3	