


CONFIDENTIAL - PROPRIETARY


"THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEM S.p.A. AND SHALL NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION"


NOTE:
- ACCURATE TRIM REQUESTED
- BENDING RADIUS: MINIMUN POSSIBLE
- ZONES WITH FLAT AND PARALLEL GEOMETRIC TOLERANCE: MEDIUM (Max ±0.3 mm) ON ALL DIRECTIONS
- THE DIMENSIONS INCLUDING THE TREATMENT











QUALITY	<6	>6 <30	>30 <120	>120 <315	>315 <1000	>1000 <2000	>2000 <4000	>4000
COARSE	±0.2	±0.5	±0.8	±1.2	±2	±3	±4	±5
MEDIUM	±0.1	±0.2	±0.3	±0.5	±0.8	±1.2	±2	±3
ACCURATE	±0.05	±0.1	±0.15	±0.2	±0.3	±0.5	±2	±3

COMMON TOLERANCE

SHORT SIDE	>3 <6	>6 <30	>30 <120	>120
ANGULAR COMMON TOLERANCE	±1°	30'	20'	10'

MATERIAL		THICKNESS mm	MODIFICATION N°	DATE
TREATMENT				SIGNATURE
	1st DRAW	DESIGN	CHECKED	TOLERANCE: MEDIUM
DATE	08/02/2021			SCALE: 1:2
SIGNATURE	Di Doi			NOT QUOTED BEVELS: 2x45°
				NOT QUOTED RADIUS: R2
				UNIT: mm
				SHEET: 1 of 1

TITLE: ASSIEME QT3500 S0 12,1"W IP69K

DRAWING N° **D02201915** | RELEASE **A** | LEVEL 00 | SIZE A2