




A		B					D				E	F	G	H		
QUALITY	<6	>30	<30	>120	<315	>1000	<2000	>4000	SHORT SIDE		<3	>6	<30	>120	NOTE - CURVATURE TRIM REQUESTED - BENDING RADIUS: MINIMUM POSSIBLE - PERPENDICULAR AND PARALLEL GEOMETRIC TOLERANCE. MEDIUM (Max. 0.3 mm) ON ALL DIRECTIONS - THE DIMENSIONS INCLUDING THE TREATMENT TOLERANCE	CONFIDENTIAL - PROPRIETARY "THIS DRAWING AND SPECIFICATION, HEREIN, ARE THE PROPERTY OF ASEM SI AND MUST BE KEPT IN STRICTLY CONFIDENTIAL MANNER IN WHOLE OR IN PART, THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION"
COMMON	COARSE	0.2	0.5	0.8	1.2	2	3	4	5	<6	<30	<120				
TOLERANCE	MEDIUM	0.1	0.2	0.3	0.5	0.8	1.2	2	3	1°	30'	20'	10'			
	ACCURATE	0.05	0.1	0.15	0.2	0.3	0.5									

MATERIAL					THICKNESS mm	MODIFICATION N°		DATE	
TREATMENT					SIGNATURE				
		1st DRAW	DESIGN	CHECKED	TOLERANCE MEDIUM		SCALE 1:4		
	DATE	10/09/2021			NOT QUOTED BEVELS 2x45°		UNIT mm	SHEET 1 of 9	OF
	SIGNATURE	Dereani			NOT QUOTED RADIUS R2				
	TITLE DIMA VK3500P-BA 24,0" VESA CON MANIGLIE								
DRAWING N° D18201927					RELEASE A		LEVEL 00		SIZE A2