

RADIAL LOAD CAPACITY (Kgs) NO AXIAL LOAD - FOR L10 LIFE OF 10,000 HOURS
Radial Load Capacity at the End of the Shaft (Kgs)

2500 RPM 1750 RPM 1150 RPM 850 RPM 220 250 290 320

AXIAL THRUST CAPACITY (Kgs) NO RADIAL LOAD - FOR L10 LIFE OF 10,000 HOURS
Horizontal Mounting Load Capacity at the End of the Shaft (Kgs)

2500 RPM 1750 RPM 1150 RPM 850 RPM 180 210 240 260

01	1020346	VS	RELEASED			
REV	ECN	BY	REVISION DESCRIPTION		CHKR	DATE
PREPARED BY		DATE	DESIGN ENGINEER		DATE	
VS		1/10/2006				
TITLE						

ES, ELEC, HPK-B1308E-SA42AA

A SIZE

Allen-Bradley

PART NO.

L13M5166ESE

OF

Notes: Print or enlarge waveforms for improved clarity. For additional specifications see L13M5166ESM.

Specifications:

- 1. Motor type: 4 pole, 3 phase, asynchronous, ventilated
- 2. Base speed: 2970 RPM.
- 3. Maximum speed: 5000 RPM.
- 4. Continuous stall torque: 115 Nm (1018 lb-in) max at 155C winding temperature in a 40C
- 5. Peak stall torque: 230 Nm (2035 lb-in) max.
- 6. Continuous output rating: 35.7 kW (hp) max at 2970 RPM. Continuous current @ 2970 RPM 91.4 Amps 0 to peak max.(64.8 Amps.RMS)
- 7. Operating voltage: 460 VAC RMS Ref. (Not for direct connection to AC line).
- 8. Continuous stall current: 91.4 Amps 0 to peak max.(64.8 Amps.RMS)
- 9. Magnetizing current: 28.8 Amps. RMS ref.
- 10. Peak stall current: 190.3 Amps 0 to peak max.(135 Amps. RMS)
- 11. Insulation class: 180 (H).
- 12. Housing temperature: 125C max.
- 13. Winding resistance: .074 Nom. Ohms, phase to phase at 20C to 30C.
- 14. Winding inductance: 5.9 mH, phase to phase Ref.
- 15. Dielectric rating of motor power connections (U,V,W), and thermostat connections (TS+, TS-) to ground: 2350 VAC RMS 50/60 Hz for 1 second.
- 16. Rotor inertia: .098 kg-m² Ref.
- 17. Rotor balancing: Quality grade G-6.3.
- 18. Product weight: 152 kg (335 lb) Ref.
- 19. Operating ambient temperature: 0C to 40C (32F to 104F).
- 20. Storage ambient temperature: -30C to 70C (-22F to 158F).
- 21. Relative humidity: 5% to 95% non-condensing.
- 22. Liquid / dust protection: IP54 with blower installed.
- 23. Shock: 10 g peak max, 6 msec duration (18 occurances tested).
- 24. Vibration: 2.5 g peak max, 30 to 2000 Hz.
- 25. Shaft material: Steel, grade 1040/1045.
- 26. Paint: Black. Shaft, key (if provided), flange mounting surface, and connectors are not painted.

Equivalent circuit parameters

X1: .298 Ohms/phs Ref at 20C to 30C.
X1: .364 Ohms/phs Ref at 20C to 30C.
Xm: 7.71 Ohms/phs Ref at 20C to 30C
R1: .037 Ohms/phs Ref at 20C to 30C
R2: .0275 Ohms/phs Ref at 20C to 30C

01	TITLE							
01								
REV	ES, ELEC, HPK-B1308E-SA42AA							
Allen-Bradley		PART N	0.					
		L13M5166ESE						
		A SIZE	SHEET	2	OF	4		

Notes: "Ref" denotes untoleranced specifications, provided for reference only.

Speed, torque and current specifications are for motor operation with Allen Bradley drives.

Feedback Specifications:

Electrical Hardware:

- 1. SIN, COS waveform output: 1024 sinusoids/rev.
- 2. SIN, COS waveform amplitude: 0.9 to 1.1 Volts peak to peak.
- 3. SIN -, COS voltage offset with respect to power input common: 2.2 to 2.8 VDC.
- 4. +5VDC voltage input: 4.5 to 12.0 VDC.
- 5. +5VDC current input: 125 mA DC max continuous, 1.0 A DC max inrush.
- 6. TS+, TS- thermostat operating voltage: 250 Volts max.
- 7. TS+, TS- thermostat operating current: 1.6/2.5 Amps max at 0.6/1.0 power factor.

Serial Communication:


- 1. DATA+, DATA- signal type, rate: RS 485, 9600 baud, asynchronous.
- 2. Communication hierarchy: Encoder is slave, communication is externally initiated.
- 3. Single turn absolute position value range: 0 to 32,767 steps (12 bit).
- 4. Absolute position data: Binary, value increases with CW shaft rotation viewing motor mounting face.
- 5. Data (byte) format: Start bit, 8 data bits, parity bit, stop bit.
- 6. Memory storage capacity: 128 bytes, EEPROM.
- 7. Encoder temperature data: Binary value of encoder temperature in degrees C.

01		TITLE						
01								
ES, ELEC, HPK-B1308E-SA42AA								
		PART N	10.					
Allen-Bradley		L13M516	66ESE					
		A SIZE	SHEET	3	OF	4		

		TORQUE					
	SPEED RPM	Tcont 460V	Tpeak 460V	Tpeak 750 V DC			
	KFIVI	Nm	Nm	Nm			
	0	115.0	229.9	229.9			
	1000	115.0	229.9	229.9			
	2300	115.0	229.9	229.9			
	2500	115.0	215.8	227.4			
	3000	115.0	178.5	186.4			

	TORQUE			
SPEED RPM	Tcont 460V	Tpeak 460V	Tpeak 750 V DC	
KPIVI	lb-in	lb-in	lb-in	
0	1018.0	2035	2035	
1000	1018.0	2035	2035	
2300	1018.0	2035	2035	
2500	1018.0	1910	2035	
3000	1018.0	1580	1650	

HPK-B1308E-SA42AA Performance with 2099-BM09 at 460 VAC and 750 V DC Drive Input, 40C Motor Ambient 260.0 240.0 220.0 200.0 180.0 TORQUE (Nm) (1.0 Nm = 8.85 lb-in) 0.001 1 14 Estimated 80.0 60.0 Tcont 460V Nm MOTOR BASE SPEED 2970 RPM Tpeak 460V Nm 40.0 'Tpeak 750 V DC Nm 20.0 0.0 500 1000 0 1500 2000 2500 3000 SPEED (RPM)



Note: Nm torque values shown are converted from tested lb-in data.