


	1	2	3	4	5	6	7	8
A	Rockwell Part Number	43PT-NJS56FS						
	Drawing	75007-055-10						
	Fiber Amplifier Diameter	2.2 mm						
	Core Diameter	2 x 1 mm						
	Flex Relief	No						
B	Fiber Optic Material	Plastic						
	Fiber Optic Type	Transmitted Beam (Individual Fiber Cable)						
	Sensing End Material	Stainless Steel						
	Fiber Tip Size	M4 & M2.6						
	Minimum Bend Radius	25 mm						
	Jacket Material	Polyethylene						
	Temperature	- 40 °C to +70 °C						
	Fiber Optic Length	2 m (78 in)						



NOTES:

- Standard Length of 78" in shown.
- Two Individual fiber cables are included per Catalog Number.
- Longer fiber optic cable lengths are available in increments of 36 inches (0.9 m) up to 50 Ft.(15.2 m). Please contact your local Rockwell Automation Distributor for More Information.

SCALE 8:1

ALL DIMENSIONS ARE MM [INCHES]

Rockwell Automation		THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.	
43pt-njs56fs.drw		Sheet 1 of 1	
PLASTIC FIBER OPTIC CABLE		Size	Ver
Drawn by: LTTS	Date: 08/02/18	C	