


	A	B
1	Rockwell Part Number	43PT-SAS56FS
2	Drawing	75007-058-01
3	Fiber Amplifier Diameter	2.2 mm
4	Core Diameter	1 mm
5	Flex Relief	No
6	Fiber Optic Material	Plastic
7	Fiber Optic Type	Transmitted Beam (Individual Fiber Cable)
8	Sensing End Material	Stainless Steel
9	Fiber Tip Size	M5x0.8 & ø4 mm
10	Minimum Bend Radius	30 mm
11	Jacket Material	Polyethylene
12	Temperature	- 30 °C to +70 °C
13	Fiber Optic Length	2 m ( 78 in)



NOTES:

- Standard Length of 78" in shown.
- Two Individual fiber cables are included per Catalog Number.
- Longer fiber optic cable lengths are available in increments of 36 inches (0.9 m) up to 50 Ft.(15.2 m).

Please contact your local Rockwell Automation Distributor for More Information.

- Do not bend the part marked with \*
- The tightening torque for the threaded part should be up to 0.8 Nm.

ALL DIMENSIONS ARE MM [INCHES]

SCALE 6:1

**Rockwell  
Automation**

43pt-sas56fs.drw  
PLASTIC FIBER OPTIC CABLE

Drawn by: LTTS

Date: 07/06/18

CONFIDENTIAL AND PROPRIETARY INFORMATION.  
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY  
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY  
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT  
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL  
AUTOMATION, INC.

Sheet 1 Of 1

Size  
C

Ver