

RADIAL LOAD CAPACITY (Kgs) NO AXIAL LOAD - FOR L10 LIFE OF 10,000 HOURS
Radial Load Capacity at the End of the Shaft (Kgs)

2500 RPM 1750 RPM 1150 RPM 850 RPM 350 390 450 500

AXIAL THRUST CAPACITY (Kgs) NO RADIAL LOAD - FOR L10 LIFE OF 10,000 HOURS
Horizontal Mounting Load Capacity at the End of the Shaft (Kgs)

2500 RPM 1750 RPM 1150 RPM 850 RPM 250 290 330 360

01	1020346	VS	RELEASED			
REV	ECN	BY	REVISION DESCRIPTION		CHKR	DATE
PREPARED BY DATE DESIGN ENGINEER					DATE	
	VS					
TITLE						

ES, ELEC, HPA-B1613C-SA42AA

Allen-Bradley

PART NO.

L16M5162ESE

A SIZE SHEET 1 OF 4

Notes: Print or enlarge waveforms for improved clarity. For additional specifications see L16M5162ESM.

#### Specifications:

- 1. Motor type: 4 pole, 3 phase, asynchronous, ventilated
- 2. Base speed: 1470 RPM.
- 3. Maximum speed: 3000 RPM.
- 4. Continuous stall torque: 271 Nm (2398 lb-in) max at 155C winding temperature in a 40C
- 5. Peak stall torque: 541.9 Nm (4796 lb-in) max.
- 6. Continuous output rating: 41.7 kW (hp) max at 1465 RPM. Continuous current @ 1470 RPM 109.8 Amps 0 to peak max.(78 Amps.RMS)
- 7. Operating voltage: 460 VAC RMS Ref. (Not for direct connection to AC line).
- 8. Continuous stall current: 109.8 Amps 0 to peak max.(78 Amps.RMS)
- 9. Magnetizing current: 31.1 Amps. RMS ref.
- 10. Peak stall current: 217 Amps 0 to peak max.( 154 Amps. RMS)
- 11. Insulation class: 180 (H).
- 12. Housing temperature: 125C max.
- 13. Winding resistance: .118 Nom. Ohms, phase to phase at 20C to 30C.
- 14. Winding inductance: 4.9 mH, phase to phase Ref.
- 15. Dielectric rating of motor power connections (U,V,W), and thermostat connections (TS+, TS-) to ground: 2350 VAC RMS 50/60 Hz for 1 second.
- 16. Rotor inertia: .206 kg-m<sup>2</sup> Ref.
- 17. Rotor balancing: Quality grade G-6.3.
- 18. Product weight: 275 kg (606 lb) Ref.
- 19. Operating ambient temperature: 0C to 40C (32F to 104F).
- 20. Storage ambient temperature: -30C to 70C (-22F to 158F).
- 21. Relative humidity: 5% to 95% non-condensing.
- 22. Liquid / dust protection: IP54 with blower installed...
- 23. Shock: 10 g peak max, 6 msec duration (18 occurances tested).
- 24. Vibration: 2.5 g peak max, 30 to 2000 Hz.
- 25. Shaft material: Steel, grade 1040/1045.
- 26. Paint: Black. Shaft, key (if provided), front mounting surface, and connectors are not painted.

# Equivalent circuit parameters

X1: .243 Ohms/phs Ref at 20C to 30C.
X1: .305 Ohms/phs Ref at 20C to 30C.
Xm: 7.35 Ohms/phs Ref at 20C to 30C
R1: .058 Ohms/phs Ref at 20C to 30C
R2: .0455 Ohms/phs Ref at 20C to 30C

01		TITLE						
UI								
REV	ES, ELEC, HPA-B1613C-SA42AA							
Allen-Bradley		PART	NO.					
		L16M51	62ESE					
		A SIZE	SHEET	2	OF	4		

Notes: "Ref" denotes untoleranced specifications, provided for reference only.

Speed, torque and current specifications are for motor operation with Allen Bradley drives.

## Feedback Specifications:

#### Electrical Hardware:

- 1. SIN, COS waveform output: 1024 sinusoids/rev.
- 2. SIN, COS waveform amplitude: 0.9 to 1.1 Volts peak to peak.
- 3. SIN -, COS voltage offset with respect to power input common: 2.2 to 2.8 VDC.
- 4. +5VDC voltage input: 4.5 to 12.0 VDC.
- 5. +5VDC current input: 125 mA DC max continuous, 1.0 A DC max inrush.
- 6. TS+, TS- thermostat operating voltage: 250 Volts max.
- 7. TS+, TS- thermostat operating current: 1.6/2.5 Amps max at 0.6/1.0 power factor.

### Serial Communication:

- 1. DATA+, DATA- signal type, rate: RS 485, 9600 baud, asynchronous.
- 2. Communication hierarchy: Encoder is slave, communication is externally initiated.
- 3. Single turn absolute position value range: 0 to 32,767 steps (12 bit).
- 4. Absolute position data: Binary, value increases with CW shaft rotation viewing motor mounting face.
- 5. Data (byte) format: Start bit, 8 data bits, parity bit, stop bit.
- 6. Memory storage capacity: 128 bytes, EEPROM.
- 7. Encoder temperature data: Binary value of encoder temperature in degrees C.


01			TITLE					
01								
REV	ES, El	LEC, HPA	A-B1613C-S	A42AA				
Allen-Bradley			PART NO	0.				
			L16M516	2ESE				
		A SIZE		SHEET	3	OF	4	


Note: "Ref" denotes untoleranced specifications, provided for reference only.

	TORQUE					
SPEED RPM	Tcont 460V	Tpeak 460V	Tpeak 750 V DC			
RPIVI	Nm	Nm	Nm			
0	271.0	541.9	541.9			
1000	271.0	541.9	541.9			
1200	271.0	541.9	541.9			
1325	271.0	480.2	535.9			
1500	271.0	395.5	423.7			

	TORQUE				
SPEED RPM	Tcont 460V Tpeak 460V		Tpeak 750 V DC		
KEW	lb-in	lb-in	lb-in		
0	2398.0	4796	4796		
1000	2398.0	4796	4796		
1200	2398.0	4796	4796		
1325	2398.0	4250	4796		
1500	2398.0	3500	3750		

# HPA-B1613C-SA42AA Performance with 2099-BM09 at 460 VAC and 750 V DCDrive Input, 40C Motor Ambient





Note: Nm torque values shown are converted from tested lb-in data.