



The Elf is a tongue-operated (or key-operated) safety interlock switch designed to fit at the leading edge of sliding, hinged or lift-off guards. The Elf's unique miniature housing (only 75 x 25 x 29 mm) makes it the smallest interlock currently available. It is designed for smaller machines such as printers, copiers and domestic machinery which, until now, have been unable to use safety interlocks due to space restrictions. With its dual entry slots and rotatable head, the versatile Elf can offer up to eight different actuator entry options.

Operation of the switch is achieved through the insertion of a specially-profiled stainless-steel key that is permanently mounted to the guard door. The semi-flexible key allows the Elf to be used on small-radii doors (60 mm or 2.36 in).

The Elf is available with a variety of contact configurations, conduit entry types and connectors. It is sealed to IP67 (watertight and dustproof). A blanking plug is supplied for the unused key entry.

Features

- Ideal for small, lightweight guards
- The smallest interlock switch available
- Contacts, 2 N.C. or 1 N.O. & 1 N.C.
- · Eight possible actuator entry points, easy to install
- Environmental protection: IP67
- · GD2 style available for demanding applications

Safety Ratings						
Standards		EN954-1, ISO13849-1, IEC/EN60204-1, NFPA79, EN1088, ISO14119, IEC/ EN60947-5-1, ANSI B11.19, AS4024.1				
Safety Classification		Dual cha	evice per E nnel interlo 4 systems	ocks suita	ble for	
Functional Safety Data * Note: For up-to-date information, visit http://www.ab.com/Safety/		B10d: > 2 x 10 ⁶ operations at min. load PFH _D : > 3 x10 ⁻⁷ MTTFd: > 385 years Dual channel interlock may be suitable for performance levels Ple or Pld (according to ISO 13849-1:2006) and for use in SIL2 or SIL3 systems (according to IEC 62061) depending on application characteristics				
Certifications			ed for all a ÜV, and C		directives,	
Outputs						
Safety Contacts * Direct Opening Action		1 N.C.		2 N.C.		
Auxiliary Contacts		1 N.O. Non		None	one	
Thermal CurrentI _{Ith}		5 A (10 A if A600)				
Rated Insulation Voltage		2500V				
Switching Current @ Voltage	, Min.	5 mA @ 5V DC				
Utilization Category						
A600/AC-15	(Ue)	600V	500V	240V	120V	
	(le)	1.2 A	1.4 A	3.0 A	6.0 A	
N600/DC-13	(Ue)	600V	500V	250V	125V	
	(le)	0.4 A	0.55 A	1.1 A	2.2 A	
Operating Characteristics						
Break Contact Force, Min.		6 N (1.35	•			
Actuation Speed, Max.			(6.29 in) pe	er sec.		
Actuation Frequency, Max.		2 cycle per sec.				
Operating Radius, Min		150 mm (5.90 in); 60 mm (2.36 in) with GD2 kit, min.				
Operating Life @ 100 mA loa	ıd	1 x 106 operations				
Environmental						
Enclosure Type Rating		IP 67				
Operating Temperature—C (F)	-20+80)° (-4+17	76°)		
Physical Characteristics						
Housing Material			oved glass	-filled PB1		
Actuator Material		Stainless	Steel			
Weight—g (oz)		60 (2.11)				
Color		Red				

- * Usable for ISO 13849-1:2006 and IEC 62061. Data other than B10d is based on:
 - Usage rate of 1op/10 mins., 24 hrs/day, 360 days/year, representing 51840 operations per year
 - Mission time/Proof test interval of 38 years
- The safety contacts are described as normally closed (N.C.) i.e., with the guard closed, actuator in place (where relevant) and the machine able to be started.



					Ca	it. No.	
	Contact			M16 C	onduit	Con	nector§
Safety	Auxiliary	Action	Actuator Type	M16	1/2 inch NPT Adaptor	Connect to Distribution Box 4-Pin Micro (M12)	Connect to ArmorBlock Guard I/O 5-Pin Micro (M12)
			Flat	440K-E33036	440K-E33029	440K-E33074	_
			_	440K-E33040	440K-E33030	440K-E33025	_
1 N.C.	1 N.O.	BBM	GD2 Metal alignment guide w/semi-flex actuator	440K-E33034	440K-E33031	440K-E33075	_
			_	440K-E33014	440K-E33053	440K-E33076	_
			Flat	440K-E33080	440K-E33037	440K-E33077	440K-E2NNFPS
			90°	440K-E33041	440K-E33045	440K-E33024	_
2 N.C.	_	_	GD2 Metal alignment guide w/semi-flex actuator	_	440K-E33046	440K-E33078	440K-E2NNAPS
			_	440K-E33047	_	440K-E33079	_

Recommended Logic Interfaces

Description	Safety Outputs	Auxiliary Outputs	Terminals	Reset Type	Power Supply	Cat. Page No.	Cat. No.
Single-Function S	afety Relays for 2 N.C	C. Contact Switch				_	
MSR127RP	3 N.O.	1 N.C.	Removable (Screw)	Monitored Manual	24V AC/DC	5-24	440R-N23135
MSR127TP	3 N.O.	1 N.C.	Removable (Screw)	Auto./Manual	24V AC/DC	5-24	440R-N23132
MSR30RT	2 N.O. Solid State	1 N.O. Solid State	Removable	Auto./Manual or Monitored Manual	24V DC	5-16	440R-N23198
Single-Function Sa	afety Relays for 1 N.C	C. & 1 N.O. Contact	Switch				
MSR9T	2 N.O.	1 N.C.	Fixed	Auto./Manual	24V AC/DC	5-14	440R-F23027
MSR33RT	2 N.O. Solid State	1 N.O.	Removable	Auto. or Monitored Manual	24V DC SELV	5-18	440R-F23200
Modular Safety Re	alays						
MSR210P Base 2 N.C. only	2 N.O.	1 N.C. and 2 PNP Solid State	Removable	Auto./Manual or Monitored Manual	24V DC from the base unit	5-74	440R-H23176
MSR220P Input Module		_	Removable	_	24V DC	5-78	440R-H23178
MSR310P Base	MSR300 Series Output Modules	3 PNP Solid State	Removable	Auto./Manual Monitored Manual	24V DC	5-94	440R-W23219
MSR320P Input Module		2 PNP Solid State	Removable	_	24V DC from the base unit	5-98	440R-W23218

Note: For additional Safety Relays connectivity, see the Safety Relays section (page 5-8) of this catalog.

For additional Safety I/O and Safety PLC connectivity, see the Programmable Safety System section (page 5-107) of this catalog.

For application and wiring diagrams, see the Safety Applications section (page 10-1) of this catalog.

Connection Systems

	Connection to E 4-Pin Mic	Connection to ArmorBlock Guard I/O 5-Pin Micro (M12)	
Description	1 N.C. & 1 N.O.	2 N.C.	2 N.C.
Cordset	889D-F4AC-*	889D-F4AC-*	_
Patchcord	889D-F4ACDM-ŵ	889D-F4ACDM-₩	889R-F5ECRM-*
Distribution Box	898D-P4‡KT-DM4	898D-4‡LT-DM4	_
Shorting Plug	898D-41KU-DM	898D-41LU-DM	_
T-Port	898D-43KY-D4	898D-43LY-D4	_

Note: For additional information, see the Safety Connection System section (page 7-1) of this catalog.



[§] For connector ratings see page 3-9.

* With a 5-pin micro (M12) connector, not all contacts are connected. See *Typical Wiring Diagram* on page 3-13 for wiring details.

^{*} Replace symbol with 2 (2 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

* Replace symbol with 1 (1 m), 2 (2 m), 3 (3 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

† Replace symbol with 4 or 8 for number of ports.


Des	Description		
	Flat Actuator, Not to be used with Metal Alignment Guide	3-52	440K-A21014
	90° Actuator, Not to be used with Metal Alignment Guide	3-52	440K-A21006
	Metal Alignment Guide with Semi-Flexible Actuator	3-52	440K-A21030
	Metal Alignment Guide	3-52	440K-A21069
	Replacement Cover	3-54	440A-A33085
	Dust Cover	3-54	440K-A17182

Approximate Dimensions—mm (inches)

Dimensions are not intended to be used for installation purposes.



3-Interlock Switches



Note: 2D, 3D and electrical drawings are available on www.ab.com/.

Desc	cription	1 N.C. & 1 N.O.	2 N.C.		
Contact Configuration		⊕ Safety A (NC) 23 24 Aux A (NO)	Safety A (NC)		
Contact Action		6 3.3 0 mm Safety A Aux A 3.8	6 3.3 0 mm Safety A Safety B		
□Open	Closed	BBM			
4-Pin Micro (M12)		1-Safety A 4-Aux A 3-Safety A	1-Safety A 4-Safety B		
5-Pin Micro (M12) For ArmorBlock Guard I/O		_	5-Safety B 2-Safety A 1-Safety A 4-Safety B		
	Brown	C-f-t- A			
Cordset	Blue	- Safety A	Safety A		
889D-F4AC- *	White	Aux A	Safety B		
	Black	Aux A	Salety B		

^{*} Replace symbol with 2 (2 m), 5 (5 m) or 10 (10 m) for standard cable lengths.





The Cadet 3 is a tongue-operated (or key-operated) safety interlock switch designed to fit at the leading edge of sliding, hinged or lift-off guards. With its dual entry slots and rotatable head, the versatile Cadet 3 can offer up to eight different actuator entry options. The unique compact housing (90.5 x 31 x 30.4 mm (3.56 x 1.22 x 1.19 in)) has industry standard DIN 50047 fixing centers for ease of mounting.

Operation of the switch is achieved through the insertion of a specially-profiled stainless-steel key that is permanently mounted to the guard door. A semi-flexible key allows the Cadet 3 to be used on small-radii doors (60 mm or 2.36 in).

Available with a variety of contact configurations, the Cadet 3 is sealed to IP67. A blanking plug is supplied for the unused key entry.

Features

- Compact size
- Ideal for small, lightweight guards
- Contacts, 2 N.C. + 1 N.O. or 3 N.C.
- Sealed to IP67
- Eight possible actuator entry points, easy to install
- Industry standard fixing centres to DIN 50047
- · GD2 style available for demanding applications

Safety Ratings							
Standards		EN954-1, ISO13849-1, IEC/EN60204-1, NFPA79, EN1088, ISO14119, IEC/ EN60947-5-1, ANSI B11.19, AS4024.1					
Safety Classification		Dual-chai	vice per E nnel interlo 4 systems	cks suitab	le for		
Functional Safety Data * Note : For up-to-date informatic visit http://www.ab.com/Safety/		B10d: > 2 x 106 operations at min. load PFH _D : > 3 x10-7 MTTFd: > 385 years Dual channel interlock may be suitable for performance levels Ple or Pld (according to ISO 13849-1:2006) and for use in SIL2 or SIL3 systems (according to IEC 62061) depending on application characteristics					
Certifications			ed for all ap ÜV, and CO		lirectives,		
Outputs							
Safety Contacts * Direct Opening Action				3 N.C.			
Auxiliary Contacts			1 N.O.				
Thermal Current I _{Ith}	•			10 A			
Rated Insulation Voltage		(Ui) 500V					
Switching Current @ Voltage, M	lin.	5 mA @ 5V DC					
Utilization Category							
A600/AC-15	(Ue)	600V	500V	240V	120V		
	(le)	1.2 A	1.4 A	3.0 A	6.0 A		
N600/DC-13	(Ue)	600V	500V	250V	125V		
	(le)	0.4 A	0.55 A	1.1 A	2.2 A		
Operating Characteristics							
Break Contact Force, Min.		15 N (3.3	7 lb)				
Actuation Speed, Max.		160 mm (6.299 in) per sec					
Actuation Frequency, Max.		2 cycle per sec.					
Operating Radius, Min		150 mm (5.905 in) (60 mm (2.36 in) with GD2 kit)					
Operating Life @ 100 mA load		1 x 106 operations					
Environmental							
Enclosure Type Rating	IP 67						
Operating Temperature—C (F)		-20+ 80° (-4+176°)					
Physical Characteristics							
Housing Material		UL appro	ved glass-	filled PBT			
Actuator Material		Stainless	Steel				
Weight—g (lbs)		80 (0.176)					
	Red						

- * Usable for ISO 13849-1:2006 and IEC 62061. Data other than B10d is based on:
 - Usage rate of 1op/10 mins., 24 hrs/day, 360 days/year, representing 51840 operations per year
 - Mission time/Proof test interval of 38 years
- The safety contacts are described as normally closed (N.C.) i.e., with the guard closed, actuator in place (where relevant) and the machine able to be started.



	Contact				Ca	it. No.	
				M16 Conduit		Connector§	
Safety	Auxiliary	Action	Actuator Type	M16	1/2 inch NPT Adaptor	Connect to Distribution Box 6-Pin Micro (M12)	Connect to ArmorBlock Guard I/O 5-Pin Micro (M12).*
			Flat	440K-C21096	440K-C21048	440K-C21090	440K-C2NNFPS
			90°	440K-C21097	440K-C21057	440K-C21091	_
3 N.C.	_	_	GD2 Metal Alignment Guide with Semi-Flex Actuator	_	440K-C21062	440K-C21092	440K-C2NNAPS
			_	440K-C21070	_	_	_
			Flat	440K-C21098	440K-C21050	440K-C21054	_
			90°	440K-C21061	440K-C21058	440K-C21067	_
		ВВМ	GD2 Metal alignment guide with semi-flex actuator	_	440K-C21074	440K-C21088	_
2 N.C.	1 N O		_	440K-C21055	_	_	_
2 N.C.	1 N.O.		Flat	440K-C21052	440K-C21093	440K-C21060	_
			90°	440K-C21065	440K-C21094	440K-C21068	_
		MBB	GD2 Metal Alignment Guide with Semi-Flex Actuator	_	440K-C21095	440K-C21089	_
			_	440K-C21080	_	_	_

Recommended Logic Interfaces

Description	Safety Outputs	Auxiliary Outputs	Terminals	Reset Type	Power Supply	Cat. Page No.	Cat. No.
Single-Function S	afety Relays						
MSR127RP	3 N.O.	1 N.C.	Removable (Screw)	Monitored Manual	24V AC/DC	5-24	440R-N23135
MSR127TP	3 N.O.	1 N.C.	Removable (Screw)	Auto./Manual	24V AC/DC	5-24	440R-N23132
MSR126T	2 N.O.	None	Fixed	Auto./Manual	24V AC/DC	5-22	440R-N23117
MSR30RT	2 N.O. Solid State	1 N.O. Solid State	Removable	Auto./Manual or Monitored Manual	24V DC	5-16	440R-N23198
Modular Safety Re	elays						
MSR210P Base 2 N.C. only	2 N.O.	1 N.C. and 2 PNP Solid State	Removable	Auto./Manual or Monitored Manual	24V DC from the base unit	5-74	440R-H23176
MSR220P Input Module	_	_	Removable	_	24V DC	5-78	440R-H23178
MSR310P Base	MSR300 Series Output Modules	3 PNP Solid State	Removable	Auto./Manual Monitored Manual	24V DC	5-94	440R-W23219
MSR320P Input Module	_	2 PNP Solid State	Removable	_	24V DC from the base unit	5-98	440R-W23218

Note: For additional Safety Relays connectivity, see the Safety Relays section (page 5-8) of this catalog.

For additional Safety I/O and Safety PLC connectivity, see the Programmable Safety System section (page 5-107) of this catalog.

For application and wiring diagrams, see the Safety Applications section (page 10-1) of this catalog.

Connection Systems

2	6-Pin Micro	5-Pin Micro
Description	(M12)	(M12)
Cordset	889R-F6ECA- *	_
Patchcord	889R-F6ECRM-*	889R-F5ECRM-*
Distribution Box	898R-P68MT-A5	_
Shorting Plug	898R-P61MU-RM	_
T-Port	NA	_

* Replace symbol with 2 (2 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

* Replace symbol with 1 (1 m), 2 (2 m), 3 (3 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

*Note: For additional information, see the Safety Connection System section (page 7-1) of this catalog.




[§] For connector ratings see page 3-9.

• With a 5-pin micro (M12) connector, not all contacts are connected. See *Typical Wiring Diagram* on page 3-17 for wiring details.

Descrip	Description				
6	Flat Actuator, Not to be used with Metal Alignment Guide	3-52	440K-A21014		
	90° Actuator, Not to be used with Metal Alignment Guide	3-52	440K-A21006		
	Metal Alignment Guide with Semi-Flexible Actuator	3-52	440K-A21030		
() () () () () () () () () ()	Replacement Cover	3-54	440A-A21115		
	Dust Cover	3-54	440K-A17182		

Approximate Dimensions—mm (inches)

Dimensions are not intended to be used for installation purposes.




Note: 2D, 3D and electrical drawings are available on www.ab.com.

Descri	iption	2 N.C. & 1 N.O.	3 N.C.	
Contact Configuration		Safety A (NC) 21 22 Safety B (NC) 33 34 Aux A (NO)	Safety A (NC) 21 22 Safety B (NC) 31 32 Safety C (NC)	
Contact Action		Safety A Safety B Aux A 3.7	3.1 0 mm	
□Open	■ Closed	Safety A Safety B Safety C 2.5	Safety A Safety B Aux A	
6-Pin Micro (M12)		3-Aux A 4-Aux A 5-Safety A	3-Safety C ———————————————————————————————————	
5-Pin Micro (M12)		_	5-Safety B 2-Safety A 1-Safety A 4-Safety B	
Red/White		C-5-h- A		
	Red/Black	Safety A	Safety A	
Cordset	Red	Safety B	Safety B	
889R-F6ECA-*	Red/Blue	Salety D	Salety D	
	Green	Aux A	Safety C	
ļ	Red/Yellow		Salety C	

 $[\]star$ Replace symbol with 2 (2 m), 5 (5 m) or 10 (10 m) for standard cable lengths.





The Trojan T15 is a compact universal tongue-operated (or key-operated) safety interlock switch designed to fit at the leading edge of sliding, hinged or lift-off guards. With its dual entry slots and rotatable head, movable only by releasing the cover screws, the Trojan T15 can offer four different options for actuator entry.

The Trojan T15 features a compact housing, only 75 x 52 x 32 mm (2.95 x 2.04 x 1.25 in) and includes direct opening action contacts and a tamper-resistant mechanism. The Trojan T15 has 2 N.C. safety contacts or 1 N.C. safety contact and 1 N.O. auxiliary contact. The unit is sealed to IP67 and has three M20 conduit entries.

Operation of the switch is achieved by the insertion of the specially-profiled stainless-steel actuator which should be permanently fixed to the leading edge of the guard door. The standard T15 incorporates actuator retention force of 30N. An optional catch mechanism helps keep doors shut on vibrating machinery.

Features

- Compact size, 75 x 52 x 32 mm (2.95 x 2.05 x 1.26 in) case
- 30 N actuator retention force
- Strong and versatile, can be used in most applications
- Contacts: 2 N.C. safety or 1 N.C. safety & 1 N.O. auxillary
- GD2 style available for demanding applications

Safety Ratings					
outer, runnings		FNQ51_1	ISO13840	-1 IFC/FN	I60204-1
Standards		EN954-1, ISO13849-1, IEC/EN60204-1, NFPA79, EN1088, ISO14119, IEC/ EN60947-5-1, ANSI B11.19, AS4024.1			
Safety Classification			vice per El suitable fo		
Functional Safety Data * Note: For up-to-date information, visit http://www.ab.com/Safety/		B10d: > 2 x 10 ⁶ operations at min. load PFH _D : > 3 x10-7 MTTFd: > 385 years Dual channel interlock may be suitable for performance levels Ple or Pld (according to ISO 13849-1:2006) and for use in SIL2 or SIL3 systems (according to IEC 62061) depending on application characteristics			
Certifications			d for all ap JV, and CC		irectives,
Outputs					
Safety Contacts * Direct Opening Action		2 N.C.		1 N.C.	
Auxiliary Contacts		None		1 N.O.	
Thermal Current I _{lth}	10 A				
Rated Insulation Voltage		(Ui) 500V			
Switching Current @ Voltage	ge, Min.	5 mA @ 5	V DC		
Utilization Category					
A600/AC-15 (Ue)	(Ue)	600V	500V	240V	120V
(le)	(le)	1.2 A	1.4 A	3.0 A	6.0 A
N600/DC-13 (Ue)	(Ue)	600V	500V	250V	125V
(le)	(le)	0.4 A	0.55 A	1.1 A	2.2 A
Operating Characteristic	S				
Break Contact Force, Min.		30 N (6.70) lb)		
Actuation Speed, Max.		160 mm (6.29 in) pe	r sec.	
Actuation Frequency, Max.		2 cycle pe	er sec.		
Operating Radius, Min		175 mm (6.89 in) 60 mm (2.36 in) with flexible actuator			
Operating Life @ 100 mA le	oad	1 x 106 or	perations		
Environmental					
Enclosure Type Rating	IP 67				
Operating Temperature—C	(F)	-20+80	° (-4+176	5°)	
Physical Characteristics					
Housing Material		UL appro	ved glass-f	illed PBT	
Actuator Material		Stainless	Steel		
Weight—g (lbs)		120 (0.26	5)		
Color		Red			

- * Usable for ISO 13849-1:2006 and IEC 62061. Data other than B10d is based on:
 - Usage rate of 1op/10 mins., 24 hrs/day, 360 days/year, representing 51840 operations per year
 - Mission time/Proof test interval of 38 years
- The safety contacts are described as normally closed (N.C.) i.e., with the guard closed, actuator in place (where relevant) and the machine able to be started.



							Cat. No.	
	Cor	ntact			M20 C	onduit	С	onnector§
Туре	Safety	Auxiliary	Contact Action	Actuator Type	M20	1/2 inch NPT Adaptor	Connect to Distribution Box 4-Pin Micro (M12)	Connect to ArmorBlock Guard I/O 5-Pin Micro (M12)
•				Standard	440K-T11303	440K-T11267	440K-T11307	440K-V2NNSPS
	2 N.C.	-	_	Fully-Flex	440K-T11395	440K-T11273	440K-T11384	440K-V2NNBPS
Trojan T15				_	440K-T11269	_	440K-T11385	_
Standard				Standard	440K-T11305	440K-T11268	440K-T11386	_
	1 N.C.	1 N.O.	BBM	Fully-Flex	440K-T11396	440K-T11276	440K-T11387	_
				_	440K-T11270	_	440K-T11388	_
				GD2 Standard	440K-T11463	440K-T11288	440K-T11389	440K-V2NNGPS-NG
	2 N.C.	-	_	Fully-Flex	440K-T11397	440K-T11287	440K-T11390	_
Trojan T15				_	440K-T11280	_	440K-T11391	_
GD2				GD2 Standard	440K-T11398	440K-T11284	440K-T11392	_
	1 N.C.	1 N.O.	BBM	Fully-Flex	440K-T11399	440K-T11283	440K-T11393	_
				_	440K-T11279	_	440K-T11394	_

[§] For connector ratings see page 3-9.

Recommended Logic Interfaces

Description	Safety Outputs	Auxiliary Outputs	Terminals	Reset Type	Power Supply	Cat. Page No.	Cat. No.
Single-Function Sa	afety Relays for 2 N.C	Contact Switch		-			
MSR127RP	3 N.O.	1 N.C.	Removable (Screw)	Monitored Manual	24V AC/DC	5-24	440R-N23135
MSR127TP	3 N.O.	1 N.C.	Removable (Screw)	Auto./Manual	24V AC/DC	5-24	440R-N23132
MSR30RT	2 N.O. Solid State	1 N.O. Solid State	Removable	Auto./Manual or Monitored Manual	24V DC	5-16	440R-N23198
Single-Function Sa	afety Relays for 1 N.C	C. & 1 N.O. Contact	Switch				
MSR9T	2 N.O.	1 N.C.	Fixed	Auto./Manual	24V AC/DC	5-14	440R-F23027
MSR33RT	2 N.O. Solid State	1 N.O.	Removable	Auto. or Monitored Manual	24V DC SELV	5-18	440R-F23200
Modular Safety Re	lays						
MSR210P Base 2 N.C. only	2 N.O.	1 N.C. and 2 PNP Solid State	Removable	Auto./Manual or Monitored Manual	24V DC from the base unit	5-74	440R-H23176
MSR220P Input Module	_	_	Removable	_	24V DC	5-78	440R-H23178
MSR310P Base	MSR300 Series Output Modules	3 PNP Solid State	Removable	Auto./Manual Monitored Manual	24V DC	5-94	440R-W23219
MSR320P Input Module	_	2 PNP Solid State	Removable	_	24V DC from the base unit	5-98	440R-W23218

Note: For additional Safety Relays connectivity, see the Safety Relays section (page 5-8) of this catalog.

For additional Safety I/O and Safety PLC connectivity, see the Programmable Safety System section (page 5-107) of this catalog.

For application and wiring diagrams, see the Safety Applications section (page 10-1) of this catalog.

Connection Systems

	Connection to 4-Pin Mi	Connection to ArmorBlock Guard I/O 5-Pin Micro (M12)	
Description	2 N.C.	1 N.C. & 1 N.O.	2 N.C.
Cordset	889D-F4AC-*	889D-F4AC-*	_
Patchcord	889D-F4ACDM-ŵ	889D-F4ACDM-ŵ	889D-F5ACDM-∗
Distribution Box	898D-4‡LT-DM4	898D-P4‡KT-DM4	_
Shorting Plug	898D-41LU-DM 898D-41KU-DM		_
T-Port	898D-43LY-D4	898D-43KY-D4	_

* Replace symbol with 2 (2 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

* Replace symbol with 1 (1 m), 2 (2 m), 3 (3 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

† Replace symbol with 4 or 8 for number of ports.


Note: For additional information, see the Safety Connection System section (page 7-1) of this catalog.




	Description	To Be Used With:	Dimensions	Cat. No.
	Standard Actuator	Trojan T15 Standard Models Only	3-51	440K-A11238
	GD2 Standard Actuator	Trojan GD2 Models Only	3-50	440G-A27011
00	GD2 Flat Actuator	Trojan GD2 Models Only	3-51	440K-A11112
	Alignment Guide with Semi-Flexible Actuator	Discard Alignment Guide for GD2 Models	3-51	440K-A11144
4	Alignment Guide with Fully-Flexible Actuator	Discard Alignment Guide for GD2 Models	3-52	440K-A27010
2000 2	Sliding Bolt Actuator	Trojan GD2 Models Only	3-55	440G-A27163
	Catch and Retainer Kit	Trojan T15 Standard Models Only	3-50	440K-A11094
A 2 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1	Replacement Cover	All Models	3-54	440A-A11499
-	Dust Cover	All Models	3-54	440K-A17180


Approximate Dimensions—mm (inches)

Dimensions are not intended to be used for installation purposes.






3-Interlock Switches



 $[\]star$ Replace symbol with 2 (2 m), 5 (5 m) or 10 (10 m) for standard cable lengths.





The Trojan family is a universal tongue-operated (or key-operated) safety-interlock switch designed to fit at the leading edge of sliding, hinged or lift-off guards. The dual key entry slots and rotatable head, movable only by releasing the cover screws, allow four actuator entry options. The Trojan contains all of the safety related functions—i.e., forced guided contacts, tamper resistant mechanism—allowing the machine to be safeguarded in compliance with the machine directive.

Operation of the switch is achieved through the insertion of a specially-profiled stainless-steel key that is permanently mounted to the leading edge of the guard door. The standard (not GD2) Trojan actuator includes a self-ejecting mechanism that prevents operation of the switch if the actuator is not mounted to the guard door (e.g., if the operator uses a spare key).

Features

- Strong and versatile, can be used in most applications
- Self-ejecting tamper resistant actuator, only operates when mounted to the guard (not with GD2 models)
- · Four possible actuator entry points, easy to install
- · GD2 style available for demanding applications

Specifications					
Safety Ratings					
Standards		EN 954-1, ISO 13849-1, IEC/EN 60204- 1, NFPA 79, EN 1088, ISO 14119, IEC/EN 60947-5-1, ANSI B11.19, AS 4024.1			
Safety Classification				dual- or Cat. 3 or	
Functional Safety Data * Note: For up-to-date information visit http://www.ab.com/Safe		PFH _D : > MTTFd: Dual cha for perfo (according for use in (according)	3 x10-7 > 385 year annel interlormance lengt to ISO 7 n SIL2 or S	rs ock may b vels Ple or 13849-1:2 GIL3 syste 52061) dep	006) and
Certifications		CE mark cULus, 7	ced for all a ΓÜV, and C	ipplicable CC	directives,
Outputs					
Safety Contacts * Direct Opening Action		3 N.C.	2 N.C.	2 N.C.	
Auxiliary Contacts		1 N.O.	2 N.O.	1 N.O.	
Thermal Current I _{Ith}		10 A	_		
Rated Insulation Voltage		(Ui) 500\	/		
Switching Current @ Voltage	, Min.	5 mA @ 5V DC			
Utilization Category	-				
Trojan 5 A300/AC-15	(Ue)	240V	120V		
	(le)	3 A	6 A		
P300/DC-13	(Ue)	250V	24V		
	(le)	0.55 A	2 A		
Trojan 6 A600/AC-15	(Ue)	600V	500V	240V	120V
	(le)	1.2 A	1.4 A	3 A	6 A
N600/DC-13	(Ue)	600V	500V	125V	24V
	(le)	0.4 A	0.55 A	2.2 A	2 A
Operating Characteristics					
Break Contact Force, Min.		Trojan 5: (6.75 lb)	12 N (2.7	lb) and 30) N
		Trojan 6:	20 N (4.5	lb)	
Actuation Speed, Max.		160 mm	(6.29 in) p	er sec	
Actuation Frequency, Max.		2 cycle			
Operating Radius, Min			(6.89 in) (2.36 in) w	rith flexible	e actuator)
Operating Life @ 100 mA loa	ıd	1 x 106 d	operations		
Environmental					
Enclosure Type Rating		IP 67			
Operating Temperature—C (F)	-20+8	0° (-4+1	76°)	
Physical Characteristics					
Housing Material			oved glass	-filled PB	Т
Actuator Material		Stainless	s Steel		
Weight—g (lbs)		160 (0.3	5)		
Color		Red			

- Usable for ISO 13849-1:2006 and IEC 62061. Data other than B10d is based on:
 - Usage rate of 1op/10 mins., 24 hrs/day, 360 days/year, representing 51840 operations per year
- Mission time/Proof test interval of 38 years
- The safety contacts are described as normally closed (N.C.) i.e., with the guard closed, actuator in place (where relevant) and the machine able to be started



							Cat. No.			
		Contact			M20 C	onduit	С	onnector§		
Туре	Safety	Auxiliary	Action	Actuator Type	M20	1/2 inch NPT Adaptor	Connect to Distribution Box 6-Pin Micro (M12)	Connect to ArmorBlock Guard I/O 5-Pin Micro (M12).*		
				Standard	440K-T11090	440K-T11202	440K-T11205	_		
			BBM	Guide/Semi- Flex	440K-T11110	440K-T11203	440K-T11206	_		
			DDIVI	Guide/Fully- Flex	440K-T11467	440K-T11204	440K-T11207	440K-T2NNBPS		
				_	440K-T11089	_	440K-T11129	_		
Trojan 5 Standard			BBM Gold Contacts	Standard	440K-T11085	_	_	_		
				Standard	440K-T11118	440K-T11208	440K-T11224	_		
			MBB	Guide/Semi- Flex	440K-T11123	440K-T11209	440K-T11363	_		
					INDB	Guide/Fully- Flex	440K-T11468	440K-T11210	440K-T11364	_
	2 N.C.	1 N.O.		_	440K-T11146	440K-T11469	440K-T11365	_		
				GD2 Standard	440K-T11336	440K-T11211	440K-T11366	440K-T2NNGPS-NG		
					BBM	Guide/Semi- Flex	440K-T11337	440K-T11212	440K-T11367	_
			DDIVI	Guide/Fully- Flex	440K-T11338	440K-T11213	440K-T11368	_		
Trojan 5 GD2				_	440K-T11147	_	440K-T11226	_		
nojan 5 GD2				GD2 Standard	440K-T11339	440K-T11470	440K-T11369	<u> </u>		
			MBB	Guide/Semi- Flex	440K-T11340	440K-T11471	440K-T11370	_		
			IVIDD	Guide/Fully- Flex	440K-T11341	440K-T11472	440K-T11371	_		
				_	440K-T11167	_	440K-T11372	_		
Trojan 5 30 N			BBM	Standard	440K-T11333	440K-T91024	440K-T11492	_		

§ For connector ratings see page 3-9. * With a 5-pin micro (M12) connector, not all contacts are connected. See *Typical Wiring Diagram* on page 3-27 for wiring details.

					Cat. No.		
		Contact			M20 C	Conduit	Connector§
Туре	Safety	Auxiliary	Action	Actuator Type	M20	1/2 inch NPT Adaptor	8-Pin Micro (M12)♣
	3 N.C.	1 N.O.	BBM	Standard	440K-T11171	440K-T11435	——————————————————————————————————————
	3 N.C.	I IN.U.	ואומט	_	440K-T11449	440K-T11408	——————————————————————————————————————
Trojan 6			BBM	Standard	440K-T11174	440K-T11438	_
	2 N.C.	2 N.O.		_	440K-T11452	440K-T11416	440K-W21BNPH
			MBB	_	440K-T11453	440K-T11454	440K-W21MNPH
			BBM	GD2 Standard	440K-T11418	440K-T11466	<u> </u>
	3 N.C.	1 N.O.	DDIVI	_	440K-T11188	440K-T11444	_
Trojan 6 GD2			MBB	_	440K-T11456	440K-T11457	<u> </u>
iiojaii 6 GD2			BBM	GD2 Standard	440K-T11445	440K-T11425	_
	2 N.C.	2 N.O.	BBIVI	_	440K-T11459	440K-T11433	440K-W21BNPH-NG
			MBB	_	440K-T11460	440K-T11461	440K-W21MNPH-NG

§ For connector ratings see page 3-9.

* With an 8-pin micro (M12) connector, not all contacts are connected. See Typical Wiring Diagram on page 3-27 for wiring details.



Recommended Logic Interfaces

Description	Safety Outputs	Auxiliary Outputs	Terminals	Reset Type	Power Supply	Cat. Page No.	Cat. No.		
Single-Function S	Single-Function Safety Relays								
MSR127RP	3 N.O.	1 N.C.	Removable (Screw)	Monitored Manual	24V AC/DC	5-24	440R-N23135		
MSR127TP	3 N.O.	1 N.C.	Removable (Screw)	Auto./Manual	24V AC/DC	5-24	440R-N23132		
MSR126T	2 N.O.	None	Fixed	Auto./Manual	24V AC/DC	5-22	440R-N23117		
MSR30RT	2 N.O. Solid State	1 N.O. Solid State	Removable	Auto./Manual or Monitored Manual	24V DC	5-16	440R-N23198		
Modular Safety R	elays								
MSR210P Base 2 N.C. only	2 N.O.	1 N.C. and 2 PNP Solid State	Removable	Auto./Manual or Monitored Manual	24V DC from the base unit	5-74	440R-H23176		
MSR220P Input Module	_	_	Removable	_	24V DC	5-78	440R-H23178		
MSR310P Base	MSR300 Series Output Modules	3 PNP Solid State	Removable	Auto./Manual Monitored Manual	24V DC	5-94	440R-W23219		
MSR320P Input Module	_	2 PNP Solid State	Removable	_	24V DC from the base unit	5-98	440R-W23218		

Note: For additional Safety Relays connectivity, see the Safety Relays section (page 5-8) of this catalog.

For additional Safety I/O and Safety PLC connectivity, see the Programmable Safety System section (page 5-107) of this catalog.

For application and wiring diagrams, see the Safety Applications section (page 10-1) of this catalog.

Connection Systems

	Tro	Trojan 6	
Description	5-Pin Micro (M12)	6-Pin Micro (M12)	8-Pin Micro (M12)
Cordset	_	889R-F6ECA-*	889D-F8AB-∗
Patchcord	889R-F5ECRM-∗	889R-F6ECRM-*	889D-F8ABDM-₩
Distribution Box	_	898R-F68MT-A5	_
Shorting Plug	_	898R-P61MU-RM	_
T-Port	_	_	_

* Replace symbol with 2 (2 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

* Replace symbol with 1 (1 m), 2 (2 m), 3 (3 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

† Replace symbol with 4 or 8 for number of ports.


Note: For additional information, see the Safety Connection System section (page 7-1) of this catalog.

	Description	To Be Used With:	Dimensions	Cat. No.
	Standard Actuator	Trojan T5 and T6 Standard Models Only	3-51	440K-A11095
	GD2 Standard Actuator	GD2 Models Only	3-50	440G-A27011
-	GD2 Flat Actuator	GD2 Models Only	3-51	440K-A11112
	Alignment Guide with Semi-Flexible Actuator	Discard Alignment Guide for GD2 Models	3-51	440K-A11144
4	Alignment Guide with Fully-Flexible Actuator	Discard Alignment Guide for GD2 Models	3-52	440K-A27010
700 1	Sliding Bolt Actuator	GD2 Models Only	3-55	440G-A27163
	Catch and Retainer Kit	Trojan T5 and T6 Standard Models Only	3-50	440K-A11094
		Trojan T5 Standard Models Only		440A-A11495
# 750E L	Replacement Cover	Trojan T5 GD2	3-54	440A-A11496
1	1	Trojan T6 Standard Models Only	4	440A-A11497
- Harrison	 	Trojan T6 GD2		440A-A11498
1	Dust Cover	All Models	3-54	440K-A17180



Approximate Dimensions—mm (inches)

Dimensions are not intended to be used for installation purposes.



Note: 2D, 3D and electrical drawings are available on www.ab.com.

3-Interlock Switches

		Trojan 5	Trojan 6		
Descr	iption	2 N.C. & 1 N.O.	2 N.C. & 2 N.O.	3 N.C. & 1 N.O.	
Contact Configuration		Safety A Safety B Aux A	Safety A 21 22 Safety B Aux A Aux B	Safety A Safety B Safety C Aux A	
Contact Action		Safety A Safety B Aux A 5.2	20 15 10 3.2 0mm Safety A Safety B Aux A Aux B	20 15 10 4.0 0mm Safety A Safety B Safety C Aux A 4.5	
□Open	■Closed	20 15 10 4.5 0mm Safety A Safety B Aux A	BBM 20 15 10 4.5 0mm Safety A Safety B Aux A Aux B 4.0	Safety A Safety B Safety C Aux B 4.0	
		MBB6-Safety B	MBB	MBB	
6-Pin Micro (M12)		3-Aux A 2-Safety B 4-Aux A 1-Safety A	_	_	
5-Pin Micro (M12) f ArmorBlock Guard I	For //O	5-Safety B 2-Safety A 1-Safety A 4-Safety B	_	_	
8-Pin Micro (M12)		_	3-NA 8-Safety A 4-Safety B 7-Aux A 5-Safety A 6-Safety B	_	
	Red/White	- Safety A	_	_	
4 Din Cordoot	Red/Black Red				
6-Pin Cordset 889R-F6ECA-∗	Red/Blue	- Safety B	_	_	
	Green	Aux	_	_	
	Red/Yellow	Λυλ		_	
	Grey Red	_	Safety A	_	
8-Pin Cordset	Yellow Pink	_	Safety B	_	
889D-F8AB-∗	White Blue	_	Aux A	_	
	Green Brown	_	NA	_	

^{*} Replace symbol with 2 (2 m), 5 (5 m) or 10 (10 m) for standard cable lengths.





The MT-GD2 family is a robust, tongue-operated (or key-operated) safety-interlock switch designed to fit at the leading edge of sliding, hinged or lift-off guards. With its dual entry slots and rotatable head, the MT-GD2 can offer eight different options for actuator entry.

The MT-GD2 features a compact housing of only 117 x 40 x 43 mm with DIN 50041 standard fixing centres and includes forced guided contacts and a tamper-resistant mechanism.


The MT-GD2 is available with a variety of contact configurations enabling it to be used as part of a system for higher-risk applications. Operation of the switch is achieved by the insertion of the specially-profiled stainless-steel actuator which should be permanently fixed to the leading edge of the guard door. An optional flexible actuator allows the MT-GD2 to operate on smaller-radii doors (≥60 mm) and a flat actuator gives additional mounting options, for example, on a chain.

A style incorporating a latch release mechanism allows manual retention of the actuator in the switch until the release mechanism is manually activated.

Features

- Strong and versatile, can be used in most applications
- Eight possible actuator entry points, easy to install
- · Variety of contact configurations
- Snap acting MT-GD2 gives a min. break contact force of 40 N
- · Optional latch release styles
- Industry standard fixing centers to DIN/EN50041

MT-GD2 Latch Release Style



Safety Ratings						
Standards	EN954-1, ISO13849-1, IEC/EN60204-1, NFPA79, EN1088, ISO14119, IEC/ EN60947-5-1, ANSI B11.19, AS4024.1					
Safety Classification				ble for Cat		
Functional Safety Data * Note : For up-to-date information visit http://www.ab.com/Safe	B10d: > 2 x 10 ⁶ operations at min. load PFH _D : > 3 x10 ⁻⁷ MTTFd: > 385 years Dual channel interlock may be suitable for performance levels Ple or Pld (according to ISO 13849-1:2006) and for use in SIL2 or SIL3 systems (according to IEC 62061) depending on application characteristics					
Certifications		CE marked for all applicable directives, cULus, TÜV, and CCC				
Outputs						
Safety Contacts *	Standard: 3 N.C. or 2 N.C. direct- opening action Snap acting: 2 N.C. direct-opening forced disconnection					
Auxiliary Contacts		Standard: 1 N.O. or 2 N.O. Snap Acting: 2 N.O.				
Thermal Current I _{lth}		10 A				
Rated Insulation Voltage		(Ui) 500\	/			
Switching Current @ Voltage	, Min.	5 mA @	5V DC			
Utilization Category						
A600/AC-15	(Ue)	600V	500V	240V	120V	
	(le)	1.2 A	1.4 A	3 A	6 A	
Standard—N600/DC-13	(Ue)	600V	500V	250V	120V	
	. ,	0.4 A	0.55 A	1.1 A	2.2 A	
Snap-Acting—A300/AC-15		240V	120V			
		3 A	6 A			
Snap-Acting—Q300/DC-13	250V	120V				
	(le)	0.27 A	0.55 A			
Operating Characteristics						
Break Contact Force, Min.	BBM & E (7.2 lbs)	MBB: 12 N Extended F tina: 40 N	lat Actuate	or:: 32 N		

Operating	Characteristics
-----------	-----------------

Break Contact Force, Min.	BBM & MBB: 12 N (2.7 lbs) BBM & Extended Flat Actuator:: 32 N (7.2 lbs) Snap acting: 40 N (9.0 lbs)			
Actuation Speed, Max.	160 mm (6.29 in) per sec.			
Actuation Frequency, Max.	2 cycle per sec			
Operating Life @ 100 mA load	1 x 106 operations			
Environmental				
Enclosure Type Rating	IP 67			
Operating Temperature—C (F)	-20+80° (-4+176°)			
Physical Characteristics				
Housing Material	Painted Zinc			
Actuator Material	Stainless Steel			
Weight—g (lbs)	520 (1.15)			
Color	Yellow or Red			

- * Usable for ISO 13849-1:2006 and IEC 62061. Data other than B10d is based on:
- Usage rate of 1op/10 mins., 24 hrs/day, 360 days/year, representing 51840 operations per year
- Mission time/Proof test interval of 38 years
- The safety contacts are described as normally closed (N.C.) i.e., with the guard closed, actuator in place (where relevant) and the machine able to be started.



Red Body Switches

					Cat. No.					
		Contact			Con	duit		Connector§		
Туре	Safety	Auxiliary	Action	Actuator Type	M20	1/2 in NPT	12-Pin M23	8-Pin Micro (M12)⊛	Connect to ArmorBlock Guard I/O 5-Pin Micro (M12)*	
				_	440K-MT55002	440K-MT55085	440K-MT55094	_	_	
	3 N.C.	1 N.O.	BBM	GD2 Standard	440K-MT55074	440K-MT55022	440K-MT55095	_	_	
	3 N.C.	I IN.O.		Fully Flexible	440K-MT55075	440K-MT55029	440K-MT55096	_	_	
			MBB	_	440K-MT55004	440K-MT55088	440K-MT55100	_	_	
				_	440K-MT55005	440K-MT55086	440K-MT55097	440K-M21BNDH	_	
			BBM	GD2 Standard	440K-MT55076	440K-MT55026	440K-MT55098	_	_	
MT-GD2				Fully Flexible	440K-MT55077	440K-MT55087	440K-MT55099	_	_	
			MBB	_	440K-MT55006	440K-MT55089	440K-MT55101	_	_	
	2 N.C.	2 N.O.		_	_	440K-M22ANDT	440K-M22ANDL	440K-M21ANDH	440K-M2NNNDS	
			Snap Acting	Extende d Flat	440K-M22AEDM	440K-M22AEDT	_	_	_	
				GD2 Standard	440K-M22ASDM	440K-M22ASDT	_	_	_	
				Fully Flexible	440K-M22ABDM	440K-M22ABDT	_	_	_	
		C. 1 N.O.		_	440K-MT55039	440K-MT55062	440K-MT55042	_	_	
	3 N.C.		BBM	GD2 Standard	440K-MT55078	440K-MT55041	440K-MT55070	_	_	
	3 N.C.			Fully Flexible	440K-MT55079	440K-MT55045	440K-MT55103	_	_	
MT-GD2 Latch			MBB	_	440K-MT55082	440K-MT55091	440K-MT55106	_	_	
Release				_	440K-MT55063	440K-MT55065	440K-MT55066	440K-M21BNDH-N5	440K-M2NNNDS-N5	
	2 N.C.	2 N.O.	BBM	GD2 Standard	440K-MT55080	440K-MT55050	440K-MT55104	_	_	
	2 14.0.	2 14.0.		Fully Flexible	440K-MT55081	440K-MT55051	440K-MT55052	_	_	
			MBB	_	440K-MT55083	440K-MT55092	440K-MT55105	440K-M21MNDH-N5	_	

§ For connector ratings see page 3-9.

* With a 5-pin micro (M12) connector, not all contacts are connected. See *Typical Wiring Diagram* on page 3-32 for wiring details.

* With an 8-pin micro (M12) connector, not all contacts are connected. See *Typical Wiring Diagram* on page 3-32 for wiring details.

Yellow Body Switches

						Cat. No.	
		Contact			Conduit	Cor	nnector§
Туре	Safety	Auxiliary	Action	Actuator Type	1/2 in NPT	12-Pin M23	5-Pin Micro (M12)∗
MT-GD2	2 N.C.	2 N.O.	Snap Acting	_	440K-M22ANYT	_	_
WH-GD2	2 IV.C.	2 N.O.	Shap Acting	Extended Flat	440K-M22AEYT	440K-M22AEYL	440K-M2NAEYS
_	2 N.C.	2 N.O.	MBB	_	440K-M22MNYT-N5	_	440K-M2NNNYS-N5

§ For connector ratings see page 3-9.

* With a 5-pin micro (M12) connector, not all contacts are connected. See *Typical Wiring Diagram* on page 3-32 for wiring details.

With an 8-pin micro (M12) connector, not all contacts are connected. See *Typical Wiring Diagram* on page 3-32 for wiring details.



Recommended Logic Interfaces

Description	Safety Outputs	Auxiliary Outputs	Terminals	Reset Type	Power Supply	Cat. Page No.	Cat. No.	
Single-Function Sa	Single-Function Safety Relays							
MSR127RP	3 N.O.	1 N.C.	Removable (Screw)	Monitored Manual	24V AC/DC	5-24	440R-N23135	
MSR127TP	3 N.O.	1 N.C.	Removable (Screw)	Auto./Manual	24V AC/DC	5-24	440R-N23132	
MSR126T	2 N.O.	None	Fixed	Auto./Manual	24V AC/DC	5-22	440R-N23117	
MSR30RT	2 N.O. Solid State	1 N.O. Solid State	Removable	Auto./Manual or Monitored Manual	24V DC	5-16	440R-N23198	
Modular Safety Re	lays							
MSR210P Base 2 N.C. only	2 N.O.	1 N.C. and 2 PNP Solid State	Removable	Auto./Manual or Monitored Manual	24V DC from the base unit	5-74	440R-H23176	
MSR220P Input Module	_	_	Removable	_	24V DC	5-78	440R-H23178	
MSR310P Base	MSR300 Series Output Modules	3 PNP Solid State	Removable	Auto./Manual Monitored Manual	24V DC	5-94	440R-W23219	
MSR320P Input Module	_	2 PNP Solid State	Removable	_	24V DC from the base unit	5-98	440R-W23218	

Note: For additional Safety Relays connectivity, see the Safety Relays section (page 5-8) of this catalog.

For additional Safety I/O and Safety PLC connectivity, see the Programmable Safety System section (page 5-107) of this catalog.

For application and wiring diagrams, see the Safety Applications section (page 10-1) of this catalog.

Connection Systems

Description	4-Pin Micro (M12)	5-Pin Micro (M12)	8-Pin Micro (M12)	12-Pin M23
Cordset	889D-F4AC-*	_	889D-F8AB-∗	889M-F12X9AE-*
Patchcord	889D-F4ACDM-₩	889R-F5ECRM-∗	889D-F8ABDM- 	_
Distribution Box	898D-P4‡LT-DM4	_	_	_
Shorting Plug	898D-41LU-DM	_	_	_
T-Port	898D-43LY-D4	_	_	_

* Replace symbol with 2 (2 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

* Replace symbol with 1 (1 m), 2 (2 m), 3 (3 m), 5 (5 m), or 10 (10 m) for standard cable lengths.

† Replace symbol with 4 or 8 for number of ports.


Note: For additional information, see the Safety Connection System section (page 7-1) of this catalog.

Description	n	Dimensions	Cat. No.
	GD2 Standard Actuator	3-50	440G-A27011
	GD2 Flat Actuator	3-51	440K-A11112
	Fully Flexible Actuator	3-50	440G-A27143
See 2	Sliding Bolt Actuator	3-55	440G-A27163
	Extended Flat Actuator	3-51	440K-A17116
	Dust Cover	3-54	440K-A17180

Approximate Dimensions—mm (inches)

Dimensions are not intended to be used for installation purposes.

MT-GD2 Latch Release



Note: 2D, 3D and electrical drawings are available on www.ab.com.

Descr	iption	2 N.C. & 1 N.O.	2 N.C. & 2 N.O.	3 N.C. & 1 N.O.	
Contact Configuration		Safety A (NC) Safety B (NC) Aux A (NO)	Safety A (NC) Safety B (NC) Aux B (NO)	Safety A Safety C Safety C	
Contact Action		20 15 10 5.2 0 mm Safety A Safety B Aux A 5.6	20 15 10 5.4 0 mm Safety A Safety B Aux A Aux B 6.0	20 15 10 5.4 0 mm Safety A Safety B Safety C Aux A 6.0	
□Open	■ Closed	BBM	Safety A Safety B Aux A Aux B Safety B Safety B Aux B Safety B Aux B Safety B Aux B Safety B	20 15 10 5.6 0 mm Safety A Safety B Safety C Aux A 5.2	
- 5,500		_	7 \$\infty\$ 5.5 0 mm Safety A Safety B Aux A Aux B 6.5 Snap Acting	_	
5-Pin Micro (M12) for Connection to ArmorBlock Guard I/O		_	5-Safety B 2-Safety A 1-Safety A 4-Safety B	_	
8-Pin Micro (M12)		_	3-Ground 2-N/A 8-Safety A 1-Aux A 4-Safety B 7-Aux A 5-Safety A 6-Safety B	_	
12-Pin Cordset	1 and 3	Safety A	Safety A	Safety A	
9	4 and 6	Safety B	Safety B	Safety B	
12 10	7 and 8	NC	Aux A	Safety C	
6 11 3 5 4	9 and 10	Aux A	Aux B	Aux A	
Pins 2, 5 and 11 are not connected.	12	Ground	Ground	Ground	
	Grey Red	_	Safety A	_	
8-Pin Cordset	Yellow Pink	_	Safety B	_	
8-Pill Coldset 889D-F8AB-∗	White Blue	_	Aux A	_	
	Green	_	Ground	_	
	Brown	_	Not Used	_	
	Brown Blue	Safety A	Safety A	Safety A	
12 Din Cordoot	White Green	Safety B	Safety B	Safety B	
12-Pin Cordset 889M-F12X9AE-*	Yellow Grey	Not Used	Aux A	Safety C	
	Pink Red	Aux A	Aux B	Aux A	
	Green/Yellow	Ground	Ground	Ground	

^{*} Replace symbol with 2 (2 m), 5 (5 m) or 10 (10 m) for standard cable lengths.

