

LEVEL		I/O CAT. NO.		MODULE LABEL															
UPPER	1769-IF8 SINGLE ENDED VOLTAGE OR CURRENT	0+		1+		2+		3+		4+		5+		6+		7+		ANL COM	
LOWER		SHIELD										ANALOG COM							
UPPER	1771-IFE 1771-IFF SINGLE ENDED	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16		
LOWER		SHIELD										MODULE COM							
UPPER	1771-IFE 1771-IFF DIFFERENTIAL 1771-IL	1+	1-	2+	2-	3+	3-	4+	4-	5+	5-	6+	6-	7+	7-	8+	8-		
LOWER		SHIELD										MODULE COM							
UPPER	1794-IE8	I-O	V-O	I-1	V-1	I-2	V-2	I-3	V-3	I-4	V-4	I-5	V-5	I-6	V-6	I-7	V-7-		
LOWER		SHIELD										+V1 COM							
UPPER	1794-IF4I 1794-OF4I	I-O	I-O RET	V-O	V-O RET	I-1	I-1 RET	V-1	V-1 RET	I-2	I-2 RET	V-2	V-2 RET	I-3	I-3 RET	V-3	V-3 RET		
LOWER		SHIELD										+V1 COM							
UPPER	1794-IF2XOF2I	IN I-O	I-O RET	IN V-O	V-O RET	IN I-1	I-1 RET	IN V-1	V-1 RET	OUT I-O	I-O RET	OUT V-O	V-O RET	OUT I-1	I-1 RET	OUT V-1	V-1 RET		
LOWER		SHIELD										+V1 COM							
UPPER	1794-IE4XOE2	IN I-O	IN V-O	IN I-1	IN V-1	IN I-2	IN V-2	IN I-3	IN V-3	OUT I-O	I-O RET	OUT V-O	V-O RET	OUT I-1	I-1 RET	OUT V-1	V-1 RET		
LOWER		SHIELD										+V1 COM							
UPPER	1756-IF8I, VOLTAGE	V-in CH0	RTN 0	V-in CH1	RTN 1	V-in CH2	RTN 2	V-in CH3	RTN 3	V-in CH4	RTN 4	V-in CH5	RTN 5	V-in CH6	RTN 6	V-in CH7	RTN 7		
LOWER		SH		SH		SH		N/C A7		SH		SH		SH		SH			
UPPER	1756-IF8I, CURRENT	I-in CH0	RTN 0	I-in CH1	RTN 1	I-in CH2	RTN 2	I-in CH3	RTN 3	I-in CH4	RTN 4	I-in CH5	RTN 5	I-in CH6	RTN 6	I-in CH7	RTN 7		
LOWER		SH		SH		SH		N/C A7		SH		SH		SH		SH			
UPPER	1756-OF8I, VOLTAGE	Vout CH0	RTN 0	Vout CH1	RTN 1	Vout CH2	RTN 2	Vout CH3	RTN 3	Vout CH4	RTN 4	Vout CH5	RTN 5	Vout CH6	RTN 6	Vout CH7	RTN 7		
LOWER		SH		SH		SH		N/C A7		SH		SH		SH		SH			
UPPER	1756-OF8I, CURRENT	Iout CH0	RTN 0	Iout CH1	RTN 1	Iout CH2	RTN 2	Iout CH3	RTN 3	Iout CH4	RTN 4	Iout CH5	RTN 5	Iout CH6	RTN 6	Iout CH7	RTN 7		
LOWER		SH		SH		SH		N/C A7		SH		SH		SH		SH			
UPPER	1756-IRT8I, RTD (3 & 4 wire sensor)	In Ch0+	In Ch0-	In Ch1+	In Ch1-	In Ch2+	In Ch2-	In Ch3+	In Ch3-	In Ch4+	In Ch4-	In Ch5+	In Ch5-	In Ch6+	In Ch6-	In Ch7+	In Ch7-		
LOWER		RTN Ch0		RTN Ch1		RTN Ch2		RTN Ch3		RTN Ch4		RTN Ch5		RTN Ch6		RTN Ch7			
UPPER	1756-IRT8I (Thermocouple)	In Ch0+	In Ch0-	In Ch1+	In Ch1-	In Ch2+	In Ch2-	In Ch3+	In Ch3-	In Ch4+	In Ch4-	In Ch5+	In Ch5-	In Ch6+	In Ch6-	In Ch7+	In Ch7-		
LOWER		SH		SH		SH		N/C A7		SH		SH		SH		SH			
UPPER	1769-L24, RTD (2_3_4 wire sensor)	EXC 0	SEN 11	SEN 12	RTN Ch0	EXC 1	SEN 11	SEN 12	RTN Ch1	EXC 2	SEN 11	V1+ OUT	V2+ OUT	I 1 OUT	I 2 OUT	COM	COM		
LOWER		SH		SH		SH		N/C A7		SH		SH		SH		SH			
UPPER	1769-L24 (VOLTAGE) (DIFFERENTIAL INPUT)	V-in CH0	RTN 0	V-in CH1	RTN 1	V-in CH2	RTN 2	V-in CH3	RTN 3	V+ 0	V+ 1	In 2	In 3			RTN 0	RTN 1		
LOWER		SH		SH		SH		N/C A7		SH		SH		SH		SH			
UPPER	NUMERIC	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16		
LOWER		17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32		
TO REORDER USE P/N W4600634501		PN-266090 																	

CUT AT 80mm

SCALE
x 1.25

NOTES:

- 1) A-B SUPPLIED ARTWORK
(CODESOFT FORMAT)
- 2) TEMPLATE CUT LINES DEPENDENT ON
CURRENT PERMANENT TOOLING.

IFM MODULE REFERENCE

1492-AIFM8-3
1492-RAIFM8-3
1492-AIFM8TC-3
1492-RAIFM8TC-3
1492-AIFM8TC-R-3
1492-RAIFM8TC-R-3

PN-266090

LABEL PART

DIMENSIONS APPLY BEFORE
SURFACE TREATMENT

(DIMENSIONS IN INCHES)
TOLERANCES UNLESS
OTHERWISE SPECIFIED

XX: N/A

XXX: N/A

ANGLES: N/A

Rockwell
Automation

IFM TERMINAL BLOCK LABEL CARD
FOR BUL. 1492 INTERFACE MODULES

Dr. M. GUELM

Date 7-28-2017

CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT
CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF
ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR
DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN
PERMISSION OF ROCKWELL AUTOMATION, INC.

Sheet 1 Of 1

Size

B

46006-345

Ver

07