






22.71±0.25
(0.5mm TYPICAL WEAR
NOT INCLUDED)

(53.2)
OVERALL HEIGHT





LIMITED DIMENSION DRAWING
THIS DRAWING SUPPLEMENTS A CAD MODEL
SEE CAD MODEL FOR ALL PART OR ASSEMBLY DETAILS
DRAWING NOTES TAKE PRIORITY OVER CAD MODEL

CRITICAL TO QUALITY CLASSIFICATION TABLE					
P=PERFORMANCE, F=FIT, A=ASSEMBLY X=IDENTIFIES APPLICABLE CLASSIFICATION(S) ◇=ENGINEERING AND/OR MANUFACTURING REQUIREMENT Ⓜ=REGULATORY REQUIREMENT-CONFORMANCE IS MANDATORY					
COMMENTS	DRAWING ZONE	P	F	A	R
ROHS	G1-H1				X

MUST COMPLY WITH ROCKWELL
AUTOMATION ENVIRONMENTAL
SPECIFICATION 970-20-01

NOTES:
1. SEE SUPPLEMENTAL ICM 10004734456
FOR REFERENCE.

A. COUMACH	1:4	XXXXX-XXX-XX	XXXXX-XX-XX	N/A		10004976197		PN-543023			
ENGINEER	SCALE	WORKMANSHIP STANDARDS	FINISH	MATERIAL			MODEL/DIR NO.		PART/MMR NUMBER		
DIMENSION UNITS-mm		ALL UNDIMENSIONED GEOMETRIES ARE CONTROLLED BY THE CAD MODEL. IN CASE OF DIMENSION DISCREPANCY, CAD MODEL OVERRIDES.		 Rockwell Automation			CONFIDENTIAL AND PROPRIETARY INFORMATION. THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL AUTOMATION, INC.				
DIMENSIONS APPLY BEFORE SURFACE TREATMENT.											
UNSPECIFIED TOLERANCES ARE AS FOLLOWS:		THIRD ANGLE PROJECTION		DESCRIPTION ICD, WHEELED PUCK, TANDEM, HP, SINGLE			DATE:2019-07-30		SHEET 1 OF 2		
.X:± 0.25							SIZE	DIR		VER	
.XX:± 0.13							B	10004734448		02	
ANG:± 0.5°											
CREATED BY:TME				CHANGED BY:TME							



CONFIDENTIAL AND PROPRIETARY INFORMATION.
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY
INFORMATION OF ROCKWELL AUTOMATION, INC. AND MAY
NOT BE USED, COPIED OR DISCLOSED TO OTHERS, EXCEPT
WITH THE AUTHORIZED WRITTEN PERMISSION OF ROCKWELL
AUTOMATION, INC.

DESCRIPTION	ICD, WHEELED PUCK, TANDEM, HP, SINGLE		DATE: 2019-07-30		SHEET 2 OF 2	
	CREATED BY: TME		CHANGED BY: TME		SIZE	VER
					B	02

10004734448